

Wireless Rugged Remote



Easy-to-Use

- The remote control operation mode enables control of 6000, SLM and ELM Series projectors. Even when the user menu on screen is switched off during the show, the off screen read out provides you with the necessary information. By connecting the Wireless Rugged Remote to an ELM or SLM lamp house, in the lamp read mode all the specific lamp parameters can be shown.
- Designed with all possible usage situations in mind, this rock solid working partner can also be mounted within a 19" equipment rack. A shoulder strap provides added convenience when climbing trusses.
- The handy carrying case contains the following items: - Rugged Remote - Charger - Supplementary mains plugs; UK/US/AUS - SUBD9 male/female adaptor - Lamp communication cable - Shoulder strap - Manual

Product specifications

WIRELESS RUGGED REMOTE

General specifications

Display	4 lines Liquid Cristal Display fully backlit
Keypad	27 keys fully backlit 5 programmable function keys
Connections	Radio frequency transceiver 2 way hardwired remote XLR port lamp module info port to facilitate spare lamp management RS 232/422 port switch RS 422T -RS 422NT -RS232
Communication (baud)	XLR fixed at 57600 bps RS 232/RS 422 (9600 bps, 19200 bps, 38400 bps, 57600 bps, 115200 bps)
Communication range	wireless up to 100m (330ft)
Address	any number between 0 and 255
Power supply	6x NiCd AA rechargeable batteries (included) or standard batteries 15-30 V DC adaptor 2 charging modes: via external charger or via XLR port of the projector power save mode = automatically switched off after 10 minutes of inactivity
Temperature range	-15 -70° c (5F -158F)
Weight	remote control: 1,3 kg (2,8 lbs) receiver: 0,3 kg (0,6 lbs)

Last updated: 08 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.