


# Input Controller 16

Input Controller 16



- 16 fully configurable inputs One output 19 inch rack mount Standard equipped with Xlite Toolset, controlling software. Multipurpose device: both Daylight Display and Projection Arrange your sources onto your display through an intuitive interface. Scale and position all sources exactly how you want them. Overlay sources using advanced chroma-keying and alpha blending features. Process video and data in pure quality onto your display. Compatible with all standard image formats.

**Product specifications****INPUT CONTROLLER 16****General specifications**

<b>Input</b>	16 user defined inputs Front accessible Integrated video processing Auto sensing, hot swappable S-video, composite, YUV, RGB SDI, HD-SDI, DVI up to UXGA
<b>Compatibility</b>	Barco Daylight Displays Projectors
<b>Output</b>	DVI-A, DVI-D, RGB
<b>Control</b>	· Scaler  16 input channels [Data-Video] fully scalable to desired output resolution · Z-order  Instant modification of Z-order control, for each output window · Window positioning  Intuitive positioning interface · Connectors  RS 232 [RJ11]
<b>Effects</b>	Anamorphic imaging Chroma-keying [per input] Alpha-keying [per input] Z-order control Windowing/ View ports
<b>Operating T°</b>	0° <> 45°
<b>Power</b>	240W-480W auto ranging 90-264V (50-60 Hz) Connector: 3 pin IEC
<b>Order Information</b>	R9851580

Last updated: 15 Mar 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.