

ELM R18 Director

Barco's ELM R18 Director combines exceptional light output and high resolution with advanced signal processing to deliver a remarkable performance breakthrough for large screen video projection.



技术规格

ELM R18 DIRECTOR

一般规格	
光输出	18000 Center lumen
分辨率	1280 x 1024 (native)
对比度	450:1 (full field)
高对比度模式	900:1 (full field)
亮度均匀性	> 90%
灯泡	3.0 kW Xenon max. lifetime: 1000 hrs typ. lifetime: 700 hrs min. lifetime: 500 hrs
噪音级别(@ 20°C -68°F)	
噪音等级 (@ 40°C -104°F)	
环境温度	Max 35°C (95°F)
功率消耗	3950 W
电源电压	200-240 V
净重	135 kg (298 lbs)
尺寸(宽x长x高)	632 x 1420 x 554 mm
灯快门装置	Standard
封装DLP™内核	not available
ScenergiX	Standard horizontal and vertical electronic edge blending
网络连接	Optional (10 base-T)
无缝切换	Standard (wipes, fades, ...)
画中画	2 sources simultaneous
数字变焦	not available
镜头编码器	on zoom, focus and lens shift
联动恒定光输出	Standard
输入源兼容性	1600 x 1200 (max. input)
固定输入	· 2x configurable 5 cable (BNC) (incl. 2 video decoders) · 2x DVI
模块化输入	Standard: 1x SDI (+ loop through) Optional: 1x HDSDI (+ loop through)
控制	· 1 x RS-232 / 422 IN · 1 x RS-232 / 422 OUT · 1 x XLR male (1 way) · 1 x XLR female (2 way) · build-in RF remote transceiver (optional) · com 800 · 10base-T (optional)
定焦镜头	LD 0.8 QLD 1.2
变焦镜头	QLD 1.5 -2.0 QLD 2.0 -2.5 QLD 2.5 -3.0 QLD 4.0 -7.0 QLD 5.6 -12.0
订购信息	R9001990

生成于: 16 Mar 2023

技术规格随时变化, 不会事先通知。请访问www.barco.com.cn, 获取更新信息。