

F50 rigging frame

Mounting rack for the F50 projector



The F50 rigging frame comes in two versions: fixed and adjustable. Different frames can easily be stacked and locked together. A truss mount is also available for safe and quick installations, both directly on the rigging frame or on the optional floor mount kit.

Product specifications**F50 RIGGING FRAME****General specifications**

Versions	adjustable (3-axis adjustable) & non-adjustable
Axis adjustment	For the adjustable version: Left/right: 4 degrees Up/down: 3 degrees
Maximum projector weight	50 kg / 110.2 lbs
Dimensions (WxLxH)	477 x 515 x 321 mm / 18.18 x 20.28 x 12.64 inches
Weight	F50 basic rental frame (non-adjustable): 7.9 kg F50 rental frame (3-axis adjustable): 10.7 kg Single point truss mount (F50 rental frame only): 4.3 kg
Safe working load (SWL)	100 kg / 220.5 lbs
Working coefficient (safety factor)	5
Certifications	Machinery directive 2006/42/EC EN ISO 12100:2010

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.