
G100-W16

17,200 lumen, WUXGA, single-chip laser phosphor projector





- single-chip high-brightness projections
- up-to-date input capabilities & future-proof design
- full operational flexibility through wide lens range

100% image performance

The G100 series opens up the possibilities of our single-chip offering with higher brightness levels than before. It brings great image quality with an impressive lumens power for bright projections indoor and outdoor. What's more, the G100 supports all the latest input sources, including HDMI 2.0, to assure deep color palettes and qualitative projections.

Thanks to Barco's Projector Toolset software, installing and managing your projector(s) can be done from the comfort of your own computer with the intuitive user interface. In addition, the Ptoolset blending and warping capabilities, make these projectors a perfect fit for multi-channel media-based attractions like planetariums, domes, theatres and projection mappings.

100% flexibility

To enable full operational versatility and effortless implementation in different project designs, the G100 comes with a stable lens holder to guarantee reliable blending and non-moving images in multichannel set-ups, and a new extensive GC-lens range supporting a throw ratio going from 0.38 up to a 10.8. It gives you flexibility to shoot from long/and or short distances, and to play with 360° orientation possibilities. The projector and its peripherals deliver the best outcomes for any creative project.

With the excellent onboard cooling the G100s can withstand a maximum ambient operating temperature of 50° C (122°F), and this all only at max. 42 dB noise levels.

100% reliability

Through its laser-phosphor light source and advanced cooling design, the G100 provides a long operating time (> 20.000 hrs) without need for lamp changes - resulting in considerable cost-savings on maintenance and consumables.

With its up-to-date and future-proof design the G100 is built to meet all your requirements in terms of image quality, reliability and sustainability.



Product specifications

G100-W16

Product specifications	G100-W15
General specifications	
Projector type	Single chip DLP laser phosphor projector
Resolution	1,920 x 1,200 (WUXGA) -0.96* DLP chip
Brightness	17,200 ISO lumen / 16,200 center lumen / 14,500 ANSI lumen
Contrast ratio	1,100:1 sequential; 5,500:1 dynamic; Extreme black: 100,000:1
Brightness uniformity	90%
Aspect ratio	16:10
Lens type	GC-lenses -0.65-0.75:1 / 0.84-1.02:1 / 1.02-1.36:1 / 1.2-1.5:1 / 1.5-2.0:1 / 2.0-4.0:1 / 4.0-7.2:1 / 7.2-10.8:1
Optical lens shift	Vertical up to 120%, depending on lens Horizontal up to 50%, depending on lens Motorized zoom and focus Motorized lens shift
Color correction	Yes
CLO (constant light output)	Yes
Light source	Laser phosphor
Light source lifetime	Up to 20,000hrs
Sealed DLP™ core	Yes
Orientation	360° rotation, no restrictions
3D	Active and passive stereoscopic 3D
Image processing	Embedded warp & blend. Also possible via Ptoolset
Keystone correction	Yes
Inputs	2x HDMI 2.0b / DisplayPort 1.2a / DVI-D / HDBaseT / 3G-SDI / VGA (D-Sub 15 pin)
Input resolutions	Up to 4K UHD @60Hz Refresh rates: 24Hz to 60Hz for WUXGA and 4KUHD (4096 x 2160 / 3860 x 2160) 4K input signals will be scaled to the projector's output resolution
Software tools	Projector Toolset*
Control	IR, RS232, RJ45, USB type A
Network connection	10/100 Ethernet, RJ45
Power requirements	100-240V / 50-60Hz
Power consumption	855W nominal, 985W maximum (@220V)
BTU per hour	2920 BTU/h nominal, 3365 BTU/h maximum (@220V)
Standby power	less than 0.5W
Noise level (typical at 25°C/77°F)	36dB(A) -40dB(A) depending on the used mode
Operating temperature	0 -50 °C (sea level)
Storage temperature	
Operating humidity	-10 to 60 °C
Operating numbers	-10 to 60 °C 10 -85% RH, non-condensing
Storage humidity	
	10 -85% RH, non-condensing
Storage humidity	10 -85% RH, non-condensing 5 -90% RH, non-condensing
Storage humidity Dimensions (WxLxH)	10 -85% RH, non-condensing 5 -90% RH, non-condensing without feet: 650 x 710 x 251 mm / 25.6 x 27.9 x 9.9 in
Storage humidity Dimensions (WxLxH) Weight	10 -85% RH, non-condensing 5 -90% RH, non-condensing without feet: 650 x 710 x 251 mm / 25.6 x 27.9 x 9.9 in without lens: 50.0 kg / 110.2 lbs
Storage humidity Dimensions (WxLxH) Weight Standard accessories	10 -85% RH, non-condensing 5 -90% RH, non-condensing without feet: 650 x 710 x 251 mm / 25.6 x 27.9 x 9.9 in without lens: 50.0 kg / 110.2 lbs Power cord, wireless remote control

Last updated: 11 Mar 2024

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.

