



MDSC-8532 SSTF / NXF

4K UHD surgical display



- **Optimized for endoscopy and surgical imaging**
- **Bright and crisp color video images**
- **Billions of true-to-life colors**
- **Accurate color-calibration s**
- **Fast power on and automatic failover**
- **'A' ecolabel for a sustainable choice**

See more with surgical 4K precision, with our 32", A-ecolabel endoscopic and surgical display. This 4K UHD display offers exceptional brightness, crisp contrast, and vivid color video images, important where morphology is inconspicuous or recessed.

Uncompromising image quality

See more subtle differences with the MDSC-8532's 4K resolution. The wide color gamut and Barco's industry-leading calibration provide a full range of true-to-life colors. And ultra-low latency ensures real-time feedback for perfect hand-eye coordination.

Fast and efficient


The MDSC-8532 is low in weight and slim in design. Its dual user interface – there is one at the front and one at the back – accommodates individual user preferences. The display is fast to power-up, low in energy consumption, and features an automatic failover.

Easily set up and change the display's layout configurations to fit your procedure. And increase efficiency with customizable shortcut buttons.

User centric design

The slim lightweight modern design features an optimized full-front glass design with bezel protection on all sides safeguards against damage by surgical lights and IV poles. It also protects the display from surgical fluids and contaminants.

The fanless design (SSTF version) and intelligent cable cover support infection control, disinfection, and cleaning. The MDSC-8532 is approved for use in the



vicinity of patients and includes an automated failover method.

It is fast to power-up and features an automatic failover. A dual interface design (front and back) accommodates individual user preference while customizable shortcuts enable faster user interactions.

The MDSC-8532 comes with a 3-year warranty and the possibility to extend this to 5, with our EssentialCare package..

Models

- MDSC-8532 SSTF: 32" 4K display with SSTP DisplayPort connectivity and fanless design, white version
- MDSC-8532 NXF: 32" 4K display with SSTP DisplayPort connectivity, fanless design and integrated Barco Nexxis Decoder (*), white version(*) Nexxis version 1.18.04 or higher

Product specificaties**MDSC-8532 SSTF / NXF**

| General specifications | |
|----------------------------------|---|
| Schermttechnologie | TFT AM LCD / LED backlight |
| Actief schermformaat (diagonaal) | 32" (813 mm) |
| Formaat actief scherm (H x V) | 708 x 399 mm |
| Beeldverhouding | 16:9 |
| Helderheid | Native: 850 cd/m ² (typical) Default setting: 550 cd/ m ² stabilized @6500K & Native color space |
| Resolutie | 3840 x 2160 pixels |
| Pixelpitch | 0.1845 mm |
| Kleurondersteuning | 1 billion (10 bit color depth) |
| Kleurenspectrum | Native: 94% NTSC |
| Kleurkalibratie | ITU-709, DCI-P3, BT.2020 (BT.2020 reproducible colors are within the limit of the LCD panel) |
| Kijkhoek | 178° Hor / 178° Ver |
| Contrastverhouding | 1350:1 (Typical) |
| Reactietijd | T _{on} + T _{off} = 18 msec (typical) |
| Wit punt | Calibrated: 5600K, 6500K, 7600K, 9300K |
| Gammacurve | Native, 1.8, 2.0, 2.2, 2.4, Video1, Video2, DICOM (review level) |
| Schermbescherming aan voorzijde | 2-side anti-reflective alkali-aluminosilicate glass with anti-fingerprint coating |
| Keyboard | Front: 5-key capacitive touch -user programmable Rear: 5-key membrane |
| Video-ingangen | <p>MDSC-8532 SSTF</p> <p>4K-UHD input:</p> <ul style="list-style-type: none"> ■ 1x DP 1.2 SST / MST up to 3840 x 2160 @ 50/60 Hz (user configurable) ■ 2x HDMI™ 2.0 up to 3840 x 2160 @ 50/60 Hz <p>FHD input (upscaled to UHD):</p> <ul style="list-style-type: none"> ■ 1x DVI ■ 1x 3G-SDI; ■ Note: DP, HDMI and DVI all support HDCP 1.4 <p>MDSC-8532 NXF</p> <p>4K-UHD input:</p> <ul style="list-style-type: none"> ■ 1x DP 1.2 SST / MST up to 3840 x 2160 @ 50/60 Hz (user configurable) ■ 1x HDMI 2.0 up to 3840 x 2160 @ 50/60 Hz <p>FHD input (upscaled to UHD):</p> <ul style="list-style-type: none"> ■ 1x DVI ■ 1x 3G-SDI; <p>· 2x FO SFP+ for 4K-UHD Nexxis link · Note: DP, HDMI and DVI all support HDCP 1.4</p> |
| Video-uitgangen | <p>MDSC-8532 SSTF and NXF</p> <ul style="list-style-type: none"> ■ 1x DP 1.2 SST (main input copy) ■ 1x 3G-SDI (loop-through) |
| Andere connectiviteit | <p>USB-A (Field FW update with USB stick)</p> <p>USB-B (remote control serial protocol)</p> <p>2x 3.5 mm minijack audio/trigger (NXF version only)</p> <p>2x USB-A keyboard/mouse (NXF version only)</p> |
| Kenmerken | User-programmable function keys, Picture-in-Picture, Picture-by-Picture, Image Mirror and Rotation, Zoom, Pan, Failover mode, User profiles, High quality upscaling from SD / FHD input to UHD, FW upload from memory stick |

Product specificaties**MDSC-8532 SSTF / NXF**

| | |
|--|--|
| Energieverbruik | MDSC-8532 SSTF Max. 100W / 25V ± 10% Low power mode: MDSC-8532 NXF Max. 110W / 25V ± 10% Low power mode: |
| Externe voeding | AC input: 100 – 240 VAC / 47-63 Hz auto-switch DC output: +25 VDC / 8 A Dimensions: 204 x 81 x 43 mm (8.0 x 3.2 x 1.7") Weight: 0.9 kg (2 lbs) |
| Uitvoer (gelijkstroom) | DP connector: +3.3 V / 500 mA USB connector: +5 V / 1 A |
| Afmetingen (B x H x D) | 768 x 480 x 79 mm (30.2 x 18.9 x 3.1") |
| Afmetingen verpakt (B x H x D) | 900 x 720 x 170 mm (35.4 x 28.3 x 6.7") |
| Net weight display | SSTF: 12.0 kg (26.5 lbs) NXF: 12.7 kg (28 lbs) |
| Nettogewicht verpakt | SSTF: 19.0 kg (41.9 lbs) NXF: 19.3 kg (42.6 lbs) |
| Montagestandaard | VESA 100 x 100 mm |
| Bedrijfstemperatuur | 0°C to 35 °C for performance 0 °C to 40 °C for safety |
| Opslagtemperatuur | -20 °C to 60 °C |
| Vochtigheid in bedrijf | 20% to 85% (non-condensing) |
| Vochtigheid bij opslag | 10% to 85% (non-condensing) |
| Bedrijfshoogte | 3000 m max. / 70 kPa |
| Opslaghoogte | 5500 m max. / 50 kPa |
| NMS Compatibility (for NXF version only) | Compatible from NMS version 1.18.04 onwards. Please always check Nexxis OR System Compatibility Matrix |
| Certificeringen | <ul style="list-style-type: none">■ Approvals/Marking:■ CE (Medical Device Class I), c-UL-us, DEMKO, CCC, BIS, INMETRO■ Green compliance: ROHS-3, REACH, WEEE■ ANSI/AAMI ES 60601-1:2005/(R)2012■ CAN/CSA-C22.2 No. 60601-1: 14■ IEC 60601-1: 2012 Edition 3.1■ EN 60601-1: 2006 + A1:2013 + A12:2014■ IEC 60601-1-2: 2014 + A1:2020■ EN 60601-1-2: 2015 + A1:2021■ FCC CFR 47 Part 15 Subpart B (Class B)■ ICES-003 (Class B)■ GB17625.1-2012; GB4943.1-2011; GB/T9254-2008■ IS 13252(Part 1):2010/ IEC 60950-1 : 2005■ UL 60950-1, 2nd Edition (to make the equivalence with NOM-019)■ ABNT NBR IEC 60601-1:2010 + Emenda 1:2016■ ABNT NBR IEC 60601-1-2:2017■ ABNT NBR IEC 60601-1-6:2011 + Emenda 1:2020■ ABNT NBR IEC 60601-1-9:2010 + Emenda 1:2014 |
| Beschermingsniveau | IP21 (IP45 front side only) |
| Garantie | 3 years |

Laatst bijgewerkt: 07 May 2024

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.