

Presto

Freestanding two- or three-channel display solution



技术规格

PRESTO

一般规格

屏幕尺寸	Two-channel: 8.7' x 3.9' / 2.66m x 1.18m Three-channel: 12.6' x 3.9' / 3.85m x 1.18m
投影机	BarcoGraphics 808s high-performance graphic projectors
分辨率	Up to 1600x1200 @ 60 Hz per channel
扫描频率	Horizontal autolock scan frequency range of 15-110 KHz Vertical autolock scan frequency of 37-200 Hz RGB bandwidth of 120 MHz (-3 dB)
投影机控制	Multilanguage on-screen menus
尺寸	Footprint: Two-channel: 9.3' W x 7.5' H x 5.6' D / 2.84m x 2.29m x 1.62m Three-channel: 13.2' W x 7.5' H x 5.3' D / 4.03m x 2.29m x 1.62m
线路电压	90-240 VAC
频率	50-60 Hz, single phase
电流	2-channel: 20 A 3-channel: 30 A
功率消耗	2,000 W / 3,000 W
净重	Net weight: 906 lb / 411 kg (2-channel) - 1,367 lb / 620 kg (3-channel) Shipping weight (rugged flight cases): 1,763 lb / 800 kg (2-channel) - 2,396 lb / 1,087 kg (3-channel)

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。