


# DCP-0810 Digital City Poster

10mm pixel pitch, 8.0m<sup>2</sup>, 320x240 pixels DOOH Billboard



The DCP-0810 is a single-piece outdoor LED advertising display system for digital out-of-home media. Thanks to Barco proprietary color signature technology, the DCP-0810 delivers an excellent balance between brightness and contrast. In this way it guarantees exact reproduction of brand colors at all times.

## Environmentally friendly

As an environmentally friendly display it ensures lower power consumption and longer lifetime. The DCP-0810 features built-in redundancies such as image failover, power supply redundancy and multiple sensors. It is also equipped with extensive remote management and control capabilities.

## For branding and advertising

The DCP-0810 provides powerful imagery in combination with 24/7 reliability and a low cost of ownership. With less power consumption and a lighter weight than similar products, the DCP-0810 is a perfect fit for advertising and branding applications.

Product specificaties

DCP-0810 DIGITAL CITY POSTER

| General specifications      |                                                   |
|-----------------------------|---------------------------------------------------|
| Pixelpitch                  | 10.2 mm                                           |
| Led-configuratie            | SMD                                               |
| Led-dichtheid               | 9,612 LED/m²                                      |
| Helderheid                  | 6,500 nits (calibrated)                           |
| Kleurverwerking             | 16 bit/color                                      |
| Kleuren                     | 281 trillion                                      |
| Hor. kijkhoek               | -70°/+70°                                         |
| Vert. kijkhoek              | -35°/+10°                                         |
| Energieverbruik (standaard) | 230 W/m²                                          |
| Warmteïssipatie (standaard) | 784 BTU/hr/m²                                     |
| Bedrijfstemperatuur         | -20°/+50°C                                        |
| Robuustheid                 | IP65 (front)                                      |
| Afmetingen (H x B x D)      | 3,264 x 2,448 x 160 mm<br>128.5 x 96.4 x 6.3 inch |
| Oppervlakte van de module   | 7.99 m²<br>86 ft²                                 |
| Gewicht / tegel             | 500 kg<br>1,102.7 lbs                             |
| Certificeringen             | CE, ETL, FCC Class A, CEBEC, RoHS                 |

Laatst bijgewerkt: 10 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer [www.barco.com](http://www.barco.com) voor de nieuwste specificaties.

