

# QSD(0.8:1) Lens



**Product specifications****QSD(0.8:1) LENS****General specifications**

Distortion	< 1%
EFL	177 mm / 6.97"
Length	221 mm / 8.7"
Max Diameter	188 mm / 7.4"
Net Weight Dimensions	3.7 kg / 8.2 lbs
Projection Distance	1.03 -4.7 m / 40 -187"
Relative Luminance	100%
Resolution	MTF > 80% @ 2.4 lp / mm 6 lp / "
Screen Width (min / max)	1 -6 m / 39 -236"
Throw Ratio	0.8

Last updated: 06 Jan 2025

© 2025 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.