



AMM 215WTD

21.5 英寸全高清外科手术显示器



- 适用于在GI内镜检查或结肠镜检查中常规筛选程序的纤巧尺寸
- 质量出众，成本效益高
- 抗菌Seolforbio技术TM

尺寸小，质量高

AMM 215WTD具有21.5英寸的小巧尺寸和高像素密度，是内窥镜相机的理想拍档。该外科手术显示器具有真正的10位实时处理、运动自适应SD和高清去隔行、先进的3D降噪和准确的彩色数据再现，符合较高的图像质量标准。

全面的连通性

AMM 215WTD支持广泛的输入类型，包括VGA、DVI、复合和S视频、RGB、分量、HD / SD SDI。

安全保障

21.5英寸手术显示器带有专有的抗菌 Seolforbio 技术TM，可防止液晶显示屏上滋生细菌和产生异味。这种注塑技术使 AMM 215WTD 符合 ISO22196 抗菌处理塑料的抗菌活性标准。

- 超高质量高分辨率LCD
- LED节能背光灯
- 支持大范围的输入
- 密封式设计符合IP23
- 抗菌Seolforbio技术TM
- 可安装的臂，符合VESA
- 逐个画面模式，可独立调整
- 保护过滤器
- DC电源
- 直观的旋转钮控制

技术规格

AMM 215WTD

一般规格

Screen technology	TFT AM LCD / LED Backlight
活跃屏幕大小 (对角线)	21.46" inches (545.2 mm)
活跃屏幕大小 (H x V)	475 x 267 mm (18.7 x 10.5")
宽高比	16:9
分辨率	1920x1080
像素间距	0.2475 mm
Color support	16.7 million
视角 (H, V)	178°
Luminance	250 cd/m2
更大灯光	1000:1
Screen protection	Double-side anti-reflective PMMA protective cover
Video input signals	2xDVI-I, VGA, RGBS / YPbPr, S-video, Composite video, 3G-SDI
Video output signals	SDI / S-video / Composite Video, RGBS / YPbPr
Power consumption (Max)	50W
Power management	Power adaptor: AC 100 ~ 240V 50-60Hz, 2.0A DC 13V, 6.92A
Dimensions display (W x H x D)	662 x 630 x 232 mm (packaged)
Net weight display	Monitor: 5.46Kg (approximately) AC adaptor: 720g
Mounting standard	VESA (100 x 100 mm)
Certifications	FDA & EC: Endoscopic and Surgical imaging (Class I) Safety: UL (UL60601-1), cUL (CAN/CSA-C22.2 No.6011-M90), CE (EN60601-1), AS/NZS 3200-1-0. CCC (GB4943-2001), CB-ITE (IEC60950-1), IP23 Compliance EMC: FCC (Part Class B), CE (EN60601-1-2), AS/NZS 3200-1-2, VCCI (Class B), CCC (GB9254, GB17625.1)
Operating temperature	32° ~ 95°F (0° ~ 35°C)
Storage temperature	-4° ~ 140°F (-20° ~ 60°C)
Operating humidity	20% ~ 80%, non-condensing
Storage humidity	10% ~ 85%, non-condensing

生成于: 08 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可, 禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新, 信息和技术规格如有变更, 恕不另行通知。请查看www.barco.com.cn以了解最新规格。