

BARCOData 708 + Iris³



技术规格

BARCODATA 708 + IRIS³

一般规格

兼容性

Horizontal autolock scan frequency of 15-69 kHz
Vertical autolock scan frequency of 37-210 Hz
Standard Video, S-Video and professional Component Video
RGB signals from a wide range of PC graphics boards with resolutions up to 1280 by 1024 pixels/60 Hz
Wideband 75 MHz RGB amplifiers
A full complement of input signal connections

对比度

>1000:1 (full field contrast)

光输出

1100 Lumen (at 10 % peak white)
130 ANSI Lumen (Economy mode)
170 ANSI Lumen (Normal mode)
200 ANSI Lumen (Boost mode)

屏幕尺寸

Min.: 1.4 m x 1.05 m (4.6' x 3.5')
Max.: 6 m x 4.5 m (20' x 15')

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。