

UDM-4K15

15,000 lumens, 4K UHD, 3-chip DLP digital large venue projector



- Dazzling colors outperforming the Rec. 709 color space
- High residual value thanks to rugged design
- Remote fleet management and connectivity with Barco Insights Management Suite
- Unified Pulse electronics with Single Step Processing

Just like the 22K version, the UDM-15K never compromises on the quality or brightness of your projection. The UDM-4K15 features 4K UHD resolution and 15,000 lumens light output to deliver impactful 4K experiences with mind-blowing colors.

Operational efficiency

Lift your creativity to unprecedented levels with the widest lens shift on the market and an extensive list of other peripherals which will facilitate a smooth installation and integration of the projector in your setup. Barco's unique FLEX² feature allows you to tune and lock the brightness level or resolution for a specific show. The modular design supports fast maintenance and easy serviceability in the field.

Pulse Electronics

With the Barco Pulse proprietary Single Step Processing technology warping, scaling and 4K UHD processing is done in only one step. The result? Razor-sharp images, market leading lowest latency, and less dark time than comparable solutions.

Connectivity

The Barco Insights Management Suite dashboard and remote log file access enables faster and more effective troubleshooting. Manage the brightness settings of your projector fleet and keep track of operating conditions anywhere and anytime through a secured cloud-based platform and integrated 3G connectivity.

Long lifetime

Thanks to its robustness and the smart material choices, you can trust UDM to withstand the endurances of life on the road. With the laser phosphor light source, lamp-related costs and maintenance as well as image flicker, belong to the past. Barco's outstanding integrated laser cooling prevents overheating and the Constant Light Output functionality guarantees constant brightness and color across the projector's lifetime.

Product specifications

UDM-4K15

General specifications

Projector type	4K UHD 3-chip DLP digital projector
Technology	0.9" DMD™ x3
Resolution	3,840 x 2,400 (4K UHD) / 2,560 x 1,600 (native) / 5,120 x 3,200 (processing)
Brightness	14,500 (4K UHD) center lumens / 14,000 ansi lumens*
	15,000 ISO lumens*
Contrast ratio	Full field 2200:1 / Barco Dyna Black 20000:1
Optical lens shift	Vertical between -100% to +130%, depending on lens Horizontal up to +/-40%, depending on lens Motorized zoom and focus (with lens memory on TLD lenses) Motorized lens shift (with position memory on all lenses)
Light source	Laser B + Red compensator and inorganic Ph wheel
Brightness uniformity	95%
Light source lifetime	30,000hr (at 100% laser power, DynaBlack = off)
Color correction	p7
Optical dowsner	Digital
Aspect ratio	16:10
Lenses	TLD+ 0.37; 0.65-0.85; 0.8-1.16; 1.25 -1.61; 1.5-2.0:1; 2.0-2.8:1; 2.8-4.5:1; 4.5-7.5:1; 7.5-11.5:1
Orientation	360°
Sealed DLP™ core	Standard
Inputs	Single HDBaseT; HDMI2.0 (HDCP2.2, HDR10); DP 1.2 (HDCP1.3); Quad 3G/12G SDI/BarcoLink ULTRA
Input resolutions	From NTSC up to 4K (4,096 x 2,160) Refresh rates: 24hz to 120hz 4K/4KUHD (4096 x 2160 / 3860 x 2400) to 240hz WQXGA (2560 x 1600)
Processing	Pulse Electronics
Picture-by-picture	Two sources simultaneously
CLO (constant light output)	Standard
DMX 512	Standard
WARP	Direct adjust OSD + toolset
ScenergiX	Horizontal and vertical edge blending
Image processing	Embedded warp & blend
Keystone correction	Yes
Integrated web server	Yes
Software tools	Projector Toolset + Android** app + iOS** app + Insights Management Suite (IMS)
Control	XLR wired + IR, RS232, Wifi**, GSM**
3D	Active eye wear (optional), passive circular (optional); 2 flash up to 200Hz; optional Dual Eye Point 240Hz
Optional Inputs	Quad DP1.2, Fiber SFP
Max. pixel clock	600 MHz
Network connection	10/100 base-T, RJ-45 connection, Wifi**
Dimensions (WxLxH)	725 x 540x 339 mm / 28.54 x 21.26 x 13.3
Weight	48 kg (105lbs) / shipping weight from factory: 61 kg (134.5 lbs)
Power requirements	120-160 V (reduced power) 15A / 200-240V (+/-10%), 8.5A, 50-60Hz
Operational humidity	0-80% (non condens)
Max. power consumption	1330W nom/ 1550w max @ 230 volts ECO STBY 1330W nom/ 1550w max @ 120 volts ECO STBY
Noise level (typical at 25°C/77°F)	46 dB(A)
Operational ambient temperature	0-40°C / 32°-104°F ***
Dissipation BTU	Max. 5,200 BTU/h
Shipping Dimensions	incl. pallet (WxLxH) 850 x 665 x 613 mm / 33.46 x 26.18 x 24.13 inches
Standard accessories	Power cord, wireless/XLR wired rugged remote control
Certifications	Compliant with UL60950-1 and EN60950-1, complies with FCC rules & regulations, part 15 Class A and CE EN55032 Class A, Rohs
Warranty	3 years
*Note	*Brightness levels +/-10%

** Wifi and GSM options are not available in all countries. Check with your Barco representative for more info.

***at higher altitude light output might be dimmed

Last updated: 30 May 2024

© 2024 Barco nv. Wszelkie prawa zastrzeżone. Powielanie w całości lub w części bez pisemnej zgody jest zabronione. Wszystkie nazwy marek i produktów są znakami towarowymi, zastrzeżonymi znakami towarowymi lub nazwami handlowymi odpowiednich właścicieli. Ze względu na ciągłe innowacje, informacje i specyfikacje techniczne mogą ulec zmianie bez wcześniejszego powiadomienia. Sprawdź www.barco.com, aby uzyskać najnowsze specyfikacje.