

# iQ R200L



## Product specifications

## IQ R200L

### General specifications

Light output	1,800 ANSI lumen
Brightness uniformity	Brightness uniformity: >95 % for the total screen
LCD panels	3 active matrix 1.3" diagonal XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1366 x 1024 pixels (aspect ratio 4:3). LCD panels are selected for a minimum of pixel defects.
Resolution	1366 x 1024 (native)
Lamp	2x 120 Watt UHP lamp, in lamp housing, pre-aligned for max. light output. Typical lifetime: 6000 h/lamp. 6000 hours in Dual Lamp Mode or max. 12000 hours/set in Single Lamp Mode.
Available Lenses	- Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (Long throw). - Variable focus lenses with a throw distance of 1.3-1.8, 1.9-2.6, 3.0-6.0 times the screen width.
Recommended Screen Width	From 1-6 m/3-20 ft.
Contrast ratio	>400 : 1 (full white/full black)
Scan Frequencies	Horizontal 15 kHz -110 kHz Vertical 25 Hz -150 Hz
Special Features	- Standard cable basket - Standard light shutter - Advanced digital zoom - Advanced picture-in-picture - Seamless switching with effects
Compatibility	-All video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43) in composite, s-VHS, component -All currently proposed HDTV extended and improved television standards (1080i, 720p...) -All computer graphics formats from VGA, S-VGA, XGA, S-XGA to U-XGA -Most Macintosh computers -Electronic Workstations with a resolution of up to 1600x1200 at 75Hz -Most sources with a pixel clock up to 160MHz -DVI sources up to SXGA
Inputs	1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video, RGBHV, RGBS, RGsB. 1x Composite Video (BNC) (up to 7 Composite Video's when using all connectors on top input board) 1x S-Video (4-pin mini-DIN) (up to 3 S-Video's when combining BNC's) 1x VGA (D15 connector) 1x DVI (Digital Visual Interface)
Communication	1x D9 connectors for RS232 In/Out 1x spherical IR receiver
Noise Level	
AC power	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
Power consumption	Max 350 Watt
Power Dissipation	
Safety Regulations	Compliant with UL1950 and EN60950
Electromagnetic Interference	BARCO's iQ Series complies with FCC rules & regulations, part 15 Class B and CE EN55022 Class B
Weight	Net weight: Body only 12.9 kg/ 28.5 lbs Shipping weight: without lens max. 17.5 kg / 38.5 lbs with lens max. 20 kg / 44 lbs

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.