

iQ Pro G400



Product specificaties

IQ PRO G400

General specifications

Lichtuitvoer	4,200 ANSI lumen
Helderheidsuniformiteit	>95 % for the total screen
Contrastverhouding	>400 : 1 (full white/full black)
Lcd-panels	3 active matrix 1.3" diagonal XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1024 x 768 pixels (aspect ratio 4:3).
Resolutie	1024 x 768 (native)
Netwerk	IQ Pro Server Specifications: -Processing Power: Pentium III socket with 1,2 Gigahertz Tualatin Celeron processor -Memory: 256 MB RAM -Storage: 40 GB hard disk -Video memory: up to 64 MB -Inputs and outputs ■ PCMCIA slot for Wireless LAN cards, memory cards, Bluetooth, input extensions ... ■ RJ45connector for Ethernet (10Mb/s) and Fast Ethernet (100Mb/s) ■ 4 USB connectors ■ Audio: 3,5 mm jacks for Microphone in, Line in and Line out
Kenmerken	- Advanced picture-in-picture - Seamless switching with effects - Standard cable basket - Standard light shutter - Advanced digital zoom
Compatibiliteit	The IQ Pro G400 is compatible with: ■ All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats ■ All currently proposed HDTV, extended and improved television standards (1080i, 720p) ■ All computer graphics formats from VGA, SVGA, XGA, SXGA to UXGA ■ Most Macintosh computers ■ Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz ■ Most computer sources with a pixel clock up to 160 MHz ■ DVI sources up to SXGA
Schermaformaat Ingangen	From 1-6 m/3-20 ft. 1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video, RGBHV, RGBS, RGBS. 1x Composite Video (BNC) (up to 7 Composite Video's when using all connectors on top input board) 1x S-Video (4-pin mini-DIN) (up to 3 S-Video's when combining BNC's) 1x VGA (D15 connector) 1x DVI (Digital Visual Interface)
Lamp	2x 250 Watt UHP lamp, in lamp housing Typical lifetime: 1000 h/lamp. 1000 hours in Dual Lamp Mode or max. 2000 hours/set in Single Lamp Mode.
Lenzen	Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (long throw). Variable focus lenses with a throw distance of 1.3-1.8, 1.9-2.6, 3.0-6.0 times the screen width
Scanfrequenties	Horizontal 15 kHz -110 kHz Vertical 25 Hz -150 Hz
Lensverschuiving	QVD Lenses Motorized V shift: -30% +120% For specific details per lens type: see lens product pages
Afmetingen (B x L x H)	Projector body with cable basket: 415 mm (Max W) x 195 mm (Max H) x 565 mm (Max D) Projector body without cable basket: 415 mm (Max W) x 195 mm (Max H) x 487 mm (Max D)
Gewicht	Net weight, body only: 12.9kg/28.5 lbs.
Communicatie	1x D9 connectors for RS232 In/Out 1x spherical IR receiver
Geluidsniveau Wisselstroom	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
Energieverbruik	Max 650 Watt
Vermogensdissipatie	Max 2219 BTU/h
Naadloos schakelen	Standard

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.