

TruePix TP1.9

1.9mmピクセルピッチの屋内用高解像度LEDディスプレイ



- **スマートエンジニアリングによって真にシームレスな映像を保証**
- **24時間365日、スムーズで効率の良い作動を保証**
- **あらゆる照明環境下で、優れた色再現度を実現**
- **環境負荷を低減**
- **最長10年間の専用サービスとサポート**

TruePix TP1.9は、Barcoの新しい主力屋内高解像度LEDプラットフォームです。27.5インチのタイルはアスペクト比16:9で、ピクセルピッチは1.9mmです。TruePixは、コントロールルーム、企業、ブロードキャストなどのビジュアライゼーション用途向けに設計されており、周囲光や制御照明に晒される環境にも対応できます。

真にシームレスな結果

TruePixは、数十年間の経験に基づいて、LEDビデオウォールが提供する体験を新たな水準へと引き上げています。このソリューションは、スマートエンジニアリングとInfinipix® Gen2、次世代のInfinipix®を組み合わせることで、意図したとおりにコンテンツを実現し、予測可能で真にシームレスな結果を保証します。24時間365日、スムーズで効率の良い作動が保証されるため、いつでも安心してご使用いただけます。

Barco TruePixのスマートエンジニアリングは、リスクのない正確な設置によって視覚的な歪みを取り除く、独自のメカニカルコンセプトを取り入れています。TruePixの卓越したシームレス性と平面性は、ガイド付きモジュール配置と自動水平調整マウントによって実現されています。Barco独自の画像処理システムであるInfinipix®の次世代製品、Infinipix® Gen2は、あらゆる輝度設定レベルにおいても優れた色再現度を保証します。また、目の疲れを軽減しながら、コンテンツのニーズを柔軟かつ自動的にサポートします。

いつでも安心

途切れることのないデータフローによって、スムーズで効率の良い作動を24時間365日保証します。EcoPowerスタンバイモードで使用すれば、二酸化炭素の排出量を削減することができます。最大10年間の専任スタッフによるサービスとサポート（均一な視覚体験を保証）で、製品寿命の最後まで安心してご使用いただけます。

技術仕様
TRUEPIX TP1.9

LED tiles	
Pixel pitch	1.906
Pixel per module	320x180 (HxV)
Aspect ratio	16:09
LED lifetime	100,000h (video -80% brightness)
Brightness	>800 nit
Peak brightness	920 nit
Internal processing	23 bit
Color depth	16 bit (281 trillion colors)
Shaders	Yes
Control	Infinpix® Gen2
Refresh rate	3,840 Hz
3D	3D supported
Frame rate	24 / 25 / 29.97 / 30 / 47.95 / 48 / 50 / 59.94 / 60 / 100 / 119.88 / 120 / 144 Hz
Hor. viewing angle	160° +/-5°
Vert. viewing angle	160° +/-5°
Brightness uniformity	>98%
Dimming	0-100%
Contrast	>11,000:1
Power consumption	647 W/m ² 136 W/Tile (max) 215.3 W/m ² 45 W/Tile (typ)
Heat dissipation	2,205 BTU/h/m ² (max) 734 BTU/h/m ² (typ)
Ceiling configurations supported?	Yes
Heat dissipation front/back	54%/46%
Operation power voltage	AC power: 100-240V 50/60Hz DC power: Input: 36-55Vdc 16A (max.) Output: 36-55Vdc 10.72A/36V (max.) or 12.55A/55V (max.)
Operational humidity	10 -80%
Operational temperature	-10°C to +40°C / 14°F to 104°F
Storage temperature	-20°C to +50°C
TAA Compliancy	Not available
Storage humidity	16 -85%
IP rating	IP30
Redundancy	Power: Optional Standard on REM tiles Data: Inter-tile and signal loop redundancy embedded / N + N redundancy optional
HDR	HLG / HDR10 supported

技術仕様**TRUEPIX TP1.9**

Concave curvature	Up to 10° standard curved tile (3.5m radius) Up to 5° curved modular tile (3.5m radius)
Convex curvature	Up to 3° standard curved tile (12m radius)
Ceiling configurations supported?	Yes
Dimensions	(WxHxD) 609.92x343.08x71mm / 24.01"x13.5"x2.80"
Weight	Standard / curved tile: 8.3kg/tile (single PSU) / 8.7kg/tile (dual PSU) / 8.2kg/tile (REM PSU) Modular curved tile: 9.1kg/tile (single PSU) 9.5kg/tile (dual PSU) / 9.0kg/tile (REM PSU)
Serviceability	Full front & full back service Modular curved tile -Full front & full back service (PSU only back access)
Cable management	No external cabling
Installation	Self-leveling with surface tolerance compensation
Module replacement	Automated parallel motorized extraction
Module placement	Guided module placement
Ergonomics	SteadyView™ driver algorithm to reduce eye fatigue
Certifications	CE, UL, FCC class A, RoHS, WEEE, REACH, CCC, RCM
TAA Compliance	Optional
Warranty	3 years
EssentialCare Service offering	10 years with LED batch compatible modules

生成日:09 Apr 2024技術仕様は予告なく変更する場合があります。最新情報については、www.barco.com をご覧ください。