

F85 series

Compact 3-chip 3D DLP projector

- **Designed for 24/7 operation**
- **Advanced processing for accurate colors**
- **Active or passive 3D up to 120 Hz**

The F85 is a compact 3-chip DLP projector that is suitable for 24/7 operation in both rental and fixed installations. Thanks to its active or passive 3D up to 120 Hz, the F85 is equally perfect for simulation applications for oil and gas, automotive prototyping and scientific research. What's more, it provides a low total cost of ownership.

High-class performance and image quality

The F85 pairs high-class performance with ultimate reliability in a compact form factor. It is available with a large range of lenses that cover different focal distances for true flexibility. Featuring high brightness levels, optical color filtering for accurate colors, 3D stereo and configurable X-PORT™ I/O and image processing, unequalled image quality is guaranteed at all times. To tailor your F85 to your specific application, you can choose from WUXGA and 1080p resolution, as well as a special projector type that can optically switch between REC709 and DCI P7 color spaces.

- 3-chip DLP® Technology
- Active 3D stereo at up to 120 Hz
- Up to 11,000 lumens
- X-PORT™ module connectivity
- Designed for 24/7 operation
- WUXGA or 1080p resolution
- Dual 400W UHP™ lamps
- Advanced Color Optical Processing (ACOP)
- RealColor™ color management
- Up to five years warranty
- Wide range of Ultra High Quality projection lenses

Product specificaties**F85 SERIES****General specifications**

Concept	Three-chip, powered lens shift system with user adjustable optical colour processing filters.
3D-mogelijkheid	Active Stereo
Resolutie	1080p (1,920 x 1,080), WUXGA (1,920 x 1,200)
Helderheid	Up to 11,000 lumens (user-configurable through lamp power and voice coil operated IRIS adjustment)
Contrast	Up to 15,000 : 1 (Fixed user-adjustable through voice coil operated IRIS F2-6 -7.0 or user activated adaptive dynamic IRIS feature)
Technologie	Three-chip DLP® projector with APOC optical color processing and user-selectable optical color space (sRGB, REC709 or optionally DCI). Individual color filters are available for R, G, and B channels for optimum color accuracy and full flexibility.
Beeldverhouding	16:9 (1080p), 16:10 (WUXGA)
Beeldschermkleuren	30-bit RGB
Latentie	~19 ms
Grafische indelingen computer	2,560 x 1,600 -640 x 480 pixel resolution / RGBHV, RGBS, RGsB / custom formats available
Horizontale scanfrequenties	10 -150kHz
Verticale scanfrequenties	48 - 190 HZ (resolution dependant)
Videoformaten	EDTV (576p, 480p), SDTV (576i, 480i), HDTV (1080p, 1080i, 720p), NTSC, PAL, SECAM
Lenswerking	Motorized zoom, focus, shift, iris and mechanical shutter
Lenzen	<ul style="list-style-type: none">■ Standard projection lens EN21■ Ultra Wide Angle lens EN22 lens■ Wide Angle Zoom EN23 lens■ Short Tele Zoom EN24 lens■ Long Tele Zoom EN23 lens
Beeldbreedte	2 -10 m
Lichtbron	400W UHP replacement lamp 1 / 400W UHP replacement lamp 2
Levensduur lamp	Up to 1,500 hours (full power) / Up to 2,000 hours (eco mode)
Computeringangen	2 x DVI-D, 2 x HDMI 1.3a, 2 x VGA, 1 x 5-BNC
Video-ingang	1 x HDMI 1.3a, 1 x YPbPr, 1 x S-video, 1 x Composite
Controlemogelijkheden	1 x RJ-45 TCP/IP, 1 x 9-pin D-SUB RS232, 1 x USB, 2 x 12V programmable trigger (3.5mm mini jack)
Afmetingen	604 x 250 x 462 mm (WxHxD)
Gewicht	24.1 kg
Verzendingsafmetingen	820 x 420 x 720 mm (WxHxD)
Verzendgewicht af fabriek	32 kg
Voedingsvereisten	100-240 V / 207 -264 VAC, 50-60 Hz / Max 1,080 W / 4.7 A @ 230 V, 4.7 A @ 240 V, 11.3A @ 100V
Conformiteiten	CE, FCC Class A, UL and cUL
Bedrijfstemperatuur	10 -40 °C
Opslagtemperatuur	-20 -60 °C
Hoogte	Up to 3,000 m
Kleur	Soft touch rubber matte black
Garantie	3 years, 500 hours or 90 days on lamp (whichever comes first). Up to 5 years total warranty available. Conditions apply.
MTBF	24,184 hours
BTU/uur	

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.