

OverView mL50

50" Display Wall system integrating TFT-LCD technology.



技术规格

OVERVIEW ML50

一般规格

电源	95-230 VAC ± 10%, 50-60 Hz
亮度均匀性	> 85 %
兼容性	BARCO®'s Display Walls integrate with the existing network environment and video sources via BARCO®'s controlware through a PanelLink™ interface
对比度	250:1
深度	1215 mm / 47.83 "
运行环境	ambient temperature 10-35°C 50-100°F humidity max. 80% (non condensing)
高度	750 mm / 29.53 "
输出频率	mains frequency 50 ... 60 Hz
灯泡	200 W metal halide short-arc lamp, integrated in a pre-adjusted lamp module, no re-adjustment after replacement operation time typ. 5,000 hours
液晶面板	Single-LCD TFT
亮度	typ. 90 cd/m ² or 200 lumens
功率消耗	260 W
分辨率	resolution per cube : VGA: 640x480 color pixels XGA: 1024x768 color pixels
安全级别	· vibrations tested according to IEC 68-3-3, IEC 68-2-2, JEAG 3605
屏幕尺寸	50" diagonal
净重	darkbox 36 kg / 79.36 lbs illumination unit 13 kg / 28.66 lbs screen module 16 kg / 35.23 lbs total module 65 kg / 143.3 lbs, distributed over 6 adjustable feet
宽度	1,000 mm / 39.37 "

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。