

# iQ R200L



## 技术规格

## IQ R200L

### 一般规格

光输出	1,800 ANSI lumen
亮度均匀性	Brightness uniformity: >95 % for the total screen
液晶面板	3 active matrix 1.3" diagonal XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1366 x 1024 pixels (aspect ratio 4:3). LCD panels are selected for a minimum of pixel defects.
分辨率	1366 x 1024 (native)
灯泡	2x 120 Watt UHP lamp, in lamp housing, pre-aligned for max. light output. Typical lifetime: 6000 h/lamp. 6000 hours in Dual Lamp Mode or max. 12000 hours/set in Single Lamp Mode.
可用镜头	· Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (Long throw). · Variable focus lenses with a throw distance of 1.3-1.8, 1.9-2.6, 3.0-6.0 times the screen width.
建议的屏幕宽度	From 1-6 m/3-20 ft.
对比度	>400 : 1 (full white/full black)
扫描频率	Horizontal 15 kHz -110 kHz Vertical 25 Hz -150 Hz
特殊性能	· Standard cable basket · Standard light shutter · Advanced digital zoom · Advanced picture-in-picture · Seamless switching with effects
兼容性	-All video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43) in composite, s-VHS, component -All currently proposed HDTV extended and improved television standards (1080i, 720p...) -All computer graphics formats from VGA, S-VGA, XGA, S-XGA to U-XGA -Most Macintosh computers -Electronic Workstations with a resolution of up to 1600x1200 at 75Hz -Most sources with a pixel clock up to 160MHz -DVI sources up to SXGA
输入	1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video, RGBHV, RGBS, RGsB. 1x Composite Video (BNC) (up to 7 Composite Video's when using all connectors on top input board) 1x S-Video (4-pin mini-DIN) (up to 3 S-Video's when combining BNC's) 1x VGA (D15 connector) 1x DVI (Digital Visual Interface)
通信	1x D9 connectors for RS232 In/Out 1x spherical IR receiver
噪音级别	
电源	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
功率消耗	Max 350 Watt
功率消耗	
安全级别	Compliant with UL1950 and EN60950
电磁干扰	BARCO's iQ Series complies with FCC rules & regulations, part 15 Class B and CE EN55022 Class B
净重	Net weight: Body only 12.9 kg / 28.5 lbs Shipping weight: without lens max. 17.5 kg / 38.5 lbs with lens max. 20 kg / 44 lbs

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可, 禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新, 信息和技术规格如有变更, 恕不另行通知。请查看[www.barco.com.cn](http://www.barco.com.cn)以了解最新规格。