

DP4K-13BLPHC

Smart Laser cinema projector for small to mid-size premium movie screens



- High-contrast images
- Reduced total cost of ownership
- Unprecedented ease of mind

The DP4K-13BLPHC doubles the contrast of the Smart Laser projector series to provide an improvement of image quality to mid-size premium screens. It delivers consistent, razor-sharp, and high-contrast images with native 4K resolution and 11,500 lumens native brightness. It's perfectly suited for small to mid-size movie screens ranging from 8 up to 13 meters (26 up to 32.7 feet).

Superior image quality

The DP4K-13BLPHC offers consistent DCI-compliant image quality with native 4K resolution, outstanding uniformity, and 5,000:1 native contrast on white and silver screens. Its light output can be dimmed to 30% of the initial brightness, enabling 2D and 3D showings from the same projector.

Reduced total cost of ownership

Eliminating all lamp-related costs, the DP4K-13BLPHC provides a very attractive TCO. Thanks to its unique cooling system, the projector boasts a 30,000-hour constant brightness at typical usage conditions.

Unprecedented ease of mind

The DP4K-13BLPHC cuts operating expenses, reduces operational complexity, and optimizes labor cost. The projector increases your uptime and frees you from all lamp-related costs, administration, and maintenance.

Product specifications**DP4K-13BLPHC****General specifications**

Brightness	11,500 lumens (typical)
Native contrast ratio	5,000:1 / 600:1 native ANSI contrast
Prime lenses	1.13-1.72; 1.35-1.86; 1.46-2.10; 1.65-2.60; 2.00-3.35
Resolution	4,096 x 2,160
Long-term brightness stability	30,000 hrs @ average usage conditions
Dimensions (WxLxH)	Projector: 754 x 1,129 x 604 mm / 29.69 x 44.5 x 23.78 inches Cooler: 561.5 x 738.5 x 348 mm / 22.11 x 29.07 x 13.7 inches
Weight	Projector: 144kg (318 lb) Cooler: 32kg (70.6 lb)
Cooling liquid hose length	4 hoses: 0.5m, 2.5m, 5m and 8m (1.6ft/8.2ft/16.4ft/26.2 ft)
Vertical separation between cooler and projector	Maximum 3m (10ft) (higher or lower)
Power requirements	Projector: single phase 200-240V 20A Cooler: obtains power from the projector
Heat load (max. power)	10796 BTU/h
Ambient temperature	35°C (95°F) Max. (projector and cooler)
Ambient humidity	85% Max. (projector and cooler)
Media server	Barco Alchemy ICMP and other IMB brands supported.
Power consumption	Projector (incl. cooler): 3.3 kW
Noise Level	dB(A) @ 1 m: 67.6 dB(A) 62 dB(A) (half fan speed)
3D systems	Active glasses systems and polarization systems on silver screens are supported. Color separation systems (Dolby3D and 6P) are not supported.
Safety requirements	Class 1 risk group 3 Show safety: the customer shall take precaution for the laser safety (respect the hazard distance and separation height) according to local laser show safety regulations. Workplace safety: the customer shall take precaution for: <ul style="list-style-type: none">workplace safety as prescribed by the local authoritiesbasic laser safety training for operatorslaser safety program implementation in the company;access limitation only to trained personnel: area labelling, etc.

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.