

OverView fPR67-DL

67" Display Wall system integrating 3-panel Poly-Silicon LCD technology with SXGA resolution. Includes front access and dual lamp.



Product specificaties

OVERVIEW FPR67-DL

General specifications	
Resolutie	SXGA
Beeldverhouding	5:4
Kleuren	16.7 millions
Lamp	• Dual lamp • 2 x 100 W • Operation time 2 x 8000 h (average) • 100% availability of display wall • Keeps track of the 2 lamp life times • Detects lamp failure • When switching from one lamp to the other, constant display quality is offered • 3 modes: Hot Stand-By: 2nd lamp is on so that the switching time in case of lamp failure of the master lamp is minimal Cold Stand-By: 2nd lamp is switched off during operation, will only be activated when a lamp failure is detected of the master lamp Auto Switch Mode: regularly switch every 500 hours
Wisselstroom	100-240 VAC, 50-60 HZ
Vermogen	• 330 W in hot standby • 220 W in cold standby
Luminantie	110 cd/m² 32 ftL
Helderheid	500 lumens
Contrast	350:1
Helderheidsuniformiteit	>95 %
Afmetingen structuur	• Diagonal 67" • Width 1335 mm / 52.56 in. • Height 1068 mm / 42.05 in. • Footprint 690 mm / 27.17 in. • Depth 822 mm / 32.36 in. • Socket heigth (min) 606 mm / 23.86 in. • Socket heigth (max) 1288 mm / 50.71 in • Weight 133 kg / 239 lbs
Naleving van milieuwetgeving	• Operating temperature: 17 °C -27 °C or 62 °F -80 °F • Humidity 40%-60%, non condensing
Toegang aan voorkant	• To engine, both lamps & filters • No limitations to install the system against a back wall
Schermen	Black type screen with large viewing angles Download the brochure for more info on the principles and technologies

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

