

# iD Pro R600

<P> </P><br>



**技术规格****ID PRO R600**

<b>一般规格</b>	
光输出	6,000 ANSI lumens
分辨率	SXGA+ (1400 x 1050)
亮度均匀性	> 95 % for the total screen
对比度	2,000 : 1 (full white/full black)
显示器	1-chip 0.95" DarkChip3™ DLP™ SXGA+ panel, with a native resolution of 1400 x 1050 pixels, 4:3 aspect ratio
特性	<ul style="list-style-type: none"><li>▪ AutoImage</li><li>▪ Advanced picture-in-picture</li><li>▪ Seamless switching with effects</li><li>▪ Standard cable basket</li></ul>
画中画	Up to 3 sources simultaneously
输入	<ul style="list-style-type: none"><li>▪ 1x Component Video, RGBHV, RGBS or RGB (5 BNC)</li><li>▪ 1x Composite Video (BNC)</li><li>▪ 1x S-Video (4-pin mini-DIN)</li><li>▪ 1x VGA (D15 connector)</li><li>▪ 1x DVI (Digital Visual Interface)</li><li>▪ 1x SDI optional</li></ul> <p>Audio connections:</p> <ul style="list-style-type: none"><li>▪ 1x Stereo mic in</li><li>▪ 1x Stereo line in</li><li>▪ 1x Stereo line out</li></ul>
输出	No output
通信	1x D9 connectors for RS232 In/Out 1x spherical IR receiver
兼容性	<ul style="list-style-type: none"><li>▪ All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats</li><li>▪ All currently proposed HDTV, extended and improved television standards (1080i, 720p)</li><li>▪ All computer graphics formats from VGA, SVGA, XGA, SXGA to UXGA</li><li>▪ Most Macintosh computers</li><li>▪ Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz</li><li>▪ Most computer sources with a pixel clock up to 160 MHz</li><li>▪ DVI sources up to SXGA+</li></ul>
输入源兼容性	1600 x 1200 (max. input)
屏幕尺寸	From 1-6m / 3-20ft.
扫描频率	Horizontal 15kHz -110 kHz Vertical 25 Hz -150 Hz
网络连接	1 x 10/100 Base-T Ethernet
机载显示器服务器	Server Specifications: -Processor: Pentium M 1,6 GHz -Memory: 512 MB DDR RAM -Storage: 40 GB hard disk -Inputs and outputs: <ul style="list-style-type: none"><li>▪ PCMCIA slot for Wireless LAN cards, memory cards, Bluetooth, input extensions ...</li><li>▪ RJ45connector for Ethernet (10Mb/s) and Fast Ethernet (100Mb/s)</li><li>▪ 4 USB connectors</li><li>▪ Audio: 3,5 mm jacks for Microphone in, Line in and Line out</li></ul>
环境温度	5°C up to 40°C

**技术规格****ID PRO R600**

灯泡	2 x 250 Watt UHP lamp, in lamp housing, pre-aligned for max. light output. Typical lifetime: 1,500 h/lamp. 1,500 hours in Dual Lamp Mode or 3,000 hours in Single Lamp Mode.
镜头	Fixed focal length lens with a throw ratio of 0.8:1 Variable focal length lenses with a throw distance of 1.1-1.3, 1.2-1.6, 1.6-2.4, 2.4-4.3 times the screen width
镜头移动	Motorized V shift: -30% +110%  For specific details per lens type: see lens product pages
镜头编码器	Not Applicable
ScenergiX	Not Applicable
封装DLP™内核	Not Applicable
灰尘过滤器	High Quality Microfilter (side removeable)
噪音级别	< 41 dB
电源电压	90V-255V
功率消耗	Max. 680 Watt
功率消耗	Max. 2400 BTU/hour
电源	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
净重	Net weight: body only: 13.5 kg/29.8 lbs
尺寸	Projector body with cable basket: 415 mm (max. W) x 195 mm (max. H) x 565 (max. D) Projector body without cable basket: 415 mm(max. W) x 195 mm (max. H) x 487 (max. D)
安全级别	Compliant with UL1950 and EN60950
电磁干扰	Compliant with FCC rules & regulations, part 15 Class B, CE EN55022 Class B and CCC

**生成于: 09 Jul 2024**

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看[www.barco.com.cn](http://www.barco.com.cn)以了解最新规格。