

SLM R6 Performer

A Compact and Smokeproof Projector for Rental & Staging Applications



- Enhanced low-light video performance is the result of its newly designed pixel map processor.
- Integrated linked Constant Light Output (CLO), which can be linked with other R6 projectors for use in multi-screen applications.
- True seamless switching includes transition effects such as cross-fade, wipe, etc. and Picture-In-Picture capability.
- The unique "click-and-play™" lenses make it possible to exchange lenses in seconds. Carrying handle with integrated rigging system. Direct stacking and interlocking design enable an easy and stable setup.
- Sealed optics significantly reduce optical system maintenance, which allows the R6 to be used at events where smoke generators are involved. Modular structure provides greater accessibility to serviceable parts.
- The optical system's compact and lightweight lens range is designed for the continuing evolution of the DLP technology.

Especificaciones del producto**SLM R6 PERFORMER**

Especificaciones generales	
Salida de luz	5.000 ANSI lumens
Digital MicroMirror Device™	3 high resolution SXGA DMD's
resolución	1280 x 1024 (native) 1600 x 1200 (max)
brillo uniforme	> 90% for the total screen area
contraste	800:1 (full white/full black)
lámpara	Lifetime (max): 1500 Hrs Lifetime (typ): 1000 Hrs Lamp power: 1,2 kW
nivel de ruido (dba) 20°C (68°F)	< 43
Nivel de ruido (a 40 °C -104 °F)	< 50
Tensión de red	110/230 V
consumo de potencia	1.600 W
temperatura ambiente	40°C (104F) max
tamaño	875 mm x 585 mm x 429 mm 34,5" x 23" x 16,9"
Peso (incluido equipo de montaje)	56 kg / 124 lbs
lentes	BARCO's "click-and-play!" TLD lenses provide the highest quality picture. Available both in fixed and zoom versions.
desplazamiento de lente	Motorized V shift: up to 100% Motorized H shift: up to 65%
núcleo DLP? estanco	Yes
Conmutación fluida	Standard
ScenergiX	Standard
Entradas fijas	· 2 Multifunctional 5-cable inputs for the connection of RGB analogue signals with standard sync (BNC connectors) or tri-level sync, sync on green or separate sync, Standard Video signals, S-VHS signals · 2 Multistandard DVI · SDI input (Serial Digital Input)
entradas opcionales	One free digital input slot for optional input modules: · SDI · HD -SDI
Mando a distancia	· RS232 or RS422 loop-through input (D9-connector) for PC based projector control · Communication input (D9-connector) for peripherals · 3 pin male XLR connector for wired remote (standard remote) · 3 pin female XLR connector for bi-directional communication (rugged remote)

Generado en: 15 Mar 2023Las especificaciones técnicas pueden estar sujetas a cambios sin previo aviso. Consulte www.barco.com para obtener la información más actual.