

MNA-240 DP 1.2 SST Encoder

4K AV-to-IP adapter for the OR and hybrid OR



- AV-to-IP conversion
- Up to 4K resolution
- Medical-grade

Adapter for the operating room

The MNA-240 DP 1.2 encoder converts DisplayPort video signals to Nexxis RAW IP packets. Other non-video signals such as audio and USB for keyboard/mouse are also supported. End-to-end video latency is amazingly short and is guaranteed not to exceed a single frame. The video streams that are distributed over the Nexxis network can go up to a resolution of 4K.

Capabilities

- AV-to-IP conversion at the source
- Seamless integration in the Nexxis environment
- Support for non-video traffic (e.g. keyboard, mouse and audio) via USB and audio connections
- Easy integration via central API provided by the Nexxis OR Management Suite NMS
- Streaming of 4K and downscaled FHD video onto the network

The MNA-240 adapters are part of Barco's Nexxis solution, which provides users with uncompromised networked visualization for the digital operating room. The compact Nexxis AV-to-IP adapters offer simplicity and flexibility while maintaining the highest possible performance standards and fitness for use in demanding medical environments.

Product specificaties

MNA-240 DP 1.2 SST ENCODER

General specifications

Videoconversie	Converts Digital video signals to uncompressed IP streams
Verwerking	Up to 4096x2160@60Hz
Kleurdiepte	8 bits / color
Latentie	Subframe
Beveiliging	AES 128 encryption of all video, data & control signals
Video-ingang	Interface: 1x DP 1.2 SST
Netwerkuitvoer	1X 4K/UHD uncompressed IP stream 1x downscaled FHD IP stream of native 4K/UHD source
IP-connectiviteit	2x 10 GbE Fiber Optic Interface with SFP+ module
IP-normen	Zeroconf, IPv4, IGMP, DHCP, RTP, RTCP, 802.1q, AES 128b, HTTP(s)
USB	1x micro-USB 2.0 + 3x USB 2.0 type-A
Audio	Line-in, line-out, headphones-out and mic-in (mono) 3.5mm connector
Nexxis-integratie	Supported from Nexxis 1.08 onwards
Voeding	External 12V Medical Approved PSU, 100-240VAC 60W, external locking
Energieverbruik	< 35W
Grootte	38 mm H x 170 mm W x 170 mm D 1.5" H x 6.7" W x 6.7" D (+/-2mm / 0.1")
Gewicht	1±0.01kg (2.20lbs)
Temperatuur	Operating: 0°C to 40°C (32°F to 104°F)
Vochtigheid	Max 85%
Opslag	Storage temperature: -20°C to 60°C (-4°F to 140°F) Storage Relative Humidity: 10% to 93%
Geluidsniveau	Typical 32dBA at 20°C at 1m
Montage	Optional VESA adapter plate or 1U rack mount for 2 devices
Certificeringen	<ul style="list-style-type: none">■ CB (IEC 60601-1) Informative report■ CB (IEC 60950-1)■ cRU, RU (cRUUs)■ Demko■ CE medical device class I■ UKCA■ BIS Registration, IS 13252 (part 1)■ KC■ BSMI■ RCM■ EAC
Standaarden	Medical Equipment: <ul style="list-style-type: none">■ IEC 60601-1:2005 + Am1:2012■ IEC 60601-1-6:2010 + Am1:2013>■ IEC 60601-1-2:2014 (ed4)■ ANSI/AAMI ES 60601-1: A1:2012 + C1:2009/(R)2012 + A2:2010/(R)2012■ CAN/CSA-C22.2 No.60601-1:14■ EN 60601-1:2006 + A1:2013 + A12:2014■ EN 60601-1-6:2010 + A1:2015■ EN 60601-1-2:2015 (ed4)■ FCC class B■ ICES-001 Level B <ul style="list-style-type: none">■ IEC 60950-1:2005 + Am1:2009 + Am2:2013■ EN 60950-1:2006 + A11:2009 + A1:2010 + A12:2011■ IS 13252

Laatst bijgewerkt: 08 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.