


G100-W22

22,000 lumen, WUXGA, single-chip laser phosphor projector



- **single-chip high-brightness projections**
- **up-to-date input capabilities & future-proof design**
- **full operational flexibility through wide lens range**

100% image performance

The G100 series opens up the possibilities of our single-chip offering with higher brightness levels than before. It brings great image quality with an impressive lumens power for bright projections indoor and outdoor. What's more, the G100 supports all the latest input sources, including HDMI 2.0, to assure deep color palettes and qualitative projections.

Thanks to Barco's Projector Toolset software, installing and managing your projector(s) can be done from the comfort of your own computer with the intuitive user interface. In addition, the Ptoolset blending and warping capabilities, make these projectors a perfect fit for multi-channel media-based attractions like planetariums, domes, theatres and projection mappings.

100% flexibility

To enable full operational versatility and effortless implementation in different project designs, the G100 comes with a stable lens holder to guarantee reliable blending and non-moving images in multi-channel set-ups, and a new extensive GC-lens range supporting a throw ratio going from 0.38 up to a 10.8. It gives you flexibility to shoot from long/and or short distances, and to play with 360° orientation possibilities. The projector and its peripherals deliver the best outcomes for any creative project.

With the excellent onboard cooling the G100s can withstand a maximum ambient operating temperature of 50°C (122°F), and this all only at max. 42 dB noise levels.

100% reliability

Through its laser-phosphor light source and advanced cooling design, the G100 provides a long operating time (> 20.000 hrs) without need for lamp changes - resulting in considerable cost-savings on maintenance and consumables.

With its up-to-date and future-proof design the G100 is built to meet all your requirements in terms of image quality, reliability and sustainability.

Product specificaties**G100-W22**

General specifications	
Type projector	Single chip DLP laser phosphor projector
Resolutie	1,920 x 1,200 (WUXGA) -0.96" DLP chip
Helderheid	22,000 ISO lumen / 20,600 center lumen / 18,500 ANSI lumen 23.750 ISO lumen (Super Bright mode)*
Contrastverhouding	1,100:1 sequential; 5,500:1 dynamic; Extreme black: 100,000:1
Helderheidsuniformiteit	90%
Beeldverhouding	16:10
Type lens	GC-lenses -0.65-0.75:1 / 0.84-1.02:1 / 1.02-1.36:1 / 1.2-1.5:1 / 1.5-2.0:1 / 2.0-4.0:1 / 4.0-7.2:1 / 7.2-10.8:1
Optische lensverschuiving	Vertical up to 120%, depending on lens Horizontal up to 50%, depending on lens Motorized zoom and focus Motorized lens shift
Kleurcorrectie	Yes
CLU (constante lichtuitvoer)	Yes
Lichtbron	Laser phosphor
Levensduur lichtbron	Up to 20,000hrs
Verzegelde DLP™-kern	Yes
Oriëntatie	360° rotation, no restrictions
3D	Active and passive stereoscopic 3D
Beeldverwerking	Embedded warp & blend. Also possible via Ptoolset
Trapeziumcorrectie	Yes
Ingangen	2x HDMI 2.0b / DisplayPort 1.2a / DVI-D / HDBaseT / 3G-SDI / VGA (D-Sub 15 pin)
Invoerresoluties	Up to 4K UHD @60Hz Refresh rates: 24Hz to 60Hz for WUXGA and 4KUHD (4096 x 2160 / 3860 x 2160) 4K input signals will be scaled to the projector's output resolution
Softwaretools	Projector Toolset**
Controle	IR, RS232, RJ45, USB type A
Netwerkverbinding	10/100 Ethernet, RJ45
Voedingsvereisten	100-240V / 50-60Hz
Energieverbruik	1200W nominal, 1380W maximum (@220V)
BTU/uur	4095 BTU/h nominal, 4710 BTU/h maximum (@220V)
Stroom in stand-by	less than 0.5W
Geluidsniveau (standaard bij 25°C/77°F)	38dB(A) -42dB(A) depending on the used mode
Bedrijfstemperatuur	0 -50 °C (sea level)
Opslagtemperatuur	-10 to 60 °C
Vochtigheid in bedrijf	10 -85% RH, non-condensing
Vochtigheid bij opslag	5 -90% RH, non-condensing
Afmetingen (B x L x H)	without feet: 650 x 710 x 251 mm / 25.6 x 27.9 x 9.9 in
Gewicht	without lens: 54 kg / 119.0 lbs
Standaardaccessoires	Power cord, wireless remote control
Certificeringen	CE, FCC Class A, cTUVUS, CCC, EAC, KCC, RCM, BIS, BSMI
Garantie	Limited 3 years parts and labor
*Opmerking	* Only available on 220V input power and with lifetime of 16.500hrs @25°C/77°F ** Integration in Ptoolset in Q1/2022

Laatst bijgewerkt: 11 Mar 2024

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.