


# Loki CinemaScope

Offering the same UHD enhancements as the Loki projector, coupled with a high-capacity 2.37:1 aspect DLP engine.



- Theater & Media Room Series
- 5K UHD Resolution (5,120 x 2,160)
- Laser Phosphor
- Up to 7,800 ANSI Lumens

Loki CinemaScope's exceptional design allows a cinemascope film to be shown without requiring an anamorphic lens. The projector also provides Barco's renowned single-step processing (SSPTM) and low latency scaling technologies.

## Professional grade optics

By basing Loki CinemaScope on a proven optical architecture, custom designed aspherical glass elements and enhanced low dispersion glass lenses, image quality is in a class of its own. Contrast is not only increased, but the details within the darkest parts of the image are more visible.

## CinemaScope

Our unique aspect ratio detection system, automatically crops and scales content to fit the appropriate screen area, ranging from 1.78:1 to 2.39:1.

Manual cropping is also available for custom configurations such as cinemascope subtitle support, where only the top black bar is removed from none 1.78:1 content, preserving the subtitles at the foot of the image.

## Laser light source

Outstanding image quality requires an exceptional light source, which is why Loki CinemaScope uses our brand-new dual laser engine.

Alongside significantly improved image uniformity, lasers last longer than traditional projector lamps, offer great image quality consistency over their lifetime, are less fragile and offer near instant on/off performance.

## Liquid cooling

Loki CinemaScope has departed from a pure fan based cooling system, opting instead for a liquid cooling PID regulation system. This combined with our simulation grade warp engine allows Balder to operate at any angle (free rotation), offering new possibilities when it comes to architectural integration.

**Product specificaties****LOKI CINEMASCOPE****General specifications**

Type projector	Single chip DLP
Technologie	0.9" DMD™
Resolutie	5,120 x 2,160 (5K UHD)
Beeldverhouding	2.37:1 (CinemaScope)
Lichtbron	Laser phosphor
Levensduur lichtbron	20,000 - 60,000 hours Laser intensity dependent
Lichtuitvoer	DCI (P3) Color Wheel: Up to 5,100 ANSI lumens T Color Wheel: Up to 6,500 ANSI lumens M Color Wheel: Up to 7,800 ANSI lumens
CLU (constante lichtuitvoer)	Yes
Contrastverhouding	1,800:1 Sequential 450:1 ANSI
Helderheidsuniformiteit	>90%
Levensbereik	(R9802232) -EN68 (0.30:1) -Periscope Lens (requires vertical installation) (R9801832) -FLDX UST (0.41:1) -90°ns (R9802244) -EN67 (0.65:1) (R9802243) -EN66 (0.80 - 1.21:1) (R9802003) -EN76 (0.95 - 1.30:1) (R9802242) -EN63 (1.20 - 1.70:1) * (R9802241) -EN61 (1.70 - 2.50:1) * (R9801211) -EN44 (2.50 - 4.60:1)  * Standard Lens Option(s)
Optische lensverschuiving	Up to 122% vertical lens shift & up to 40% horizontal lens shift (depending on lens selection)  Visit the Barco Residential Lens Calculator for further information Download Lens & Airflow Data Here
Optische dowser	Yes
Kleurcorrectie	P7 RealColor™
Kleurenspectrum	DCI (P3) Color Wheel: DCI P3 T Color Wheel: REC.709 M Color Wheel: REC.709
Beeldverwerking	Embedded Warp & Blend Engine
WARP	4-Corner Warp & Bow Correction via Warp Engine
Oriëntatie	360° Rotation
Netwerkverbinding	10/100 Ethernet via RJ45 connection
Geïntegreerde webserver	Yes
Diagnose	via Prospector web interface
HDR	HDR10
3D	Active Stereoscopic 3D Additional hardware required please contact an authorized Barco representative for details
Ingangen	1 x HDMI 2.0 (HDCP 2.2) 1 x HDBaseT (HDCP 1.4 -9Gbps only) 2 x Dual Link DVI-D 2 x Display Port (1.2) 12G-SDI  1 x RJ45 Ethernet 1 x RS232 1 x Remote Control (RC) 3 x USB (2 x Rear, 1 x Front) DMX (1 x Input, 1 x Output)
Invoerresoluties	From VGA up to 4K UHD (3,840 x 2,160) @ 60Hz or up to 2,560 x 1,600 @ 120Hz
Latentie	TBD
Controle	IR, RS232, IP, 12v Trigger Driver modules available for: Crestron, Control4, RTI & Savant  NOTE: 12v Trigger(s) do not follow standard functionality and require an IP command to enable / disable them. Download our integration guide for more information.
Voedingsvereisten	100 -240V / 50 -60Hz US Requires: 20A Service (NEMA 5-20P Plug Type)
Energieverbruik	2180 W -Maximum
BTU/uur	Max. 6,000 BTU/h
Stroom in stand-by	Standby ECO Mode: 110v -0.78W (with LAN Connection) 230v -0.87W (with LAN Connection)

**Product specificaties****LOKI CINEMASCOPE**

Geluidsniveau (standaard bij 25°C/77°F)	38 dB(A)
Bedrijfstemperatuur	10 to 45 °C at Sea Level Optimal Set Point: 20 °C
Operationele vochtigheid	20 to 80% (relative humidity)
Luchtstroomvereisten	Air Inlet (from Rear w/Feet Down): Right Side Exhaust (from Rear w/Feet Down): Rear  Clearance Requirements: Front: 1cm Left: 1cm Right: 50cm Rear: 100cm Top: 1cm
Luchtuitstroom	193 ft <sup>3</sup> /min @ 25 °C 327 m <sup>3</sup> /hour @ 25 °C <a href="#">Download Lens &amp; Airflow Data Here</a>
Afmetingen (B x L x H)	Excluding Lens 577 x 738 x 304 mm 22.7 x 29.1 x 12 in.
Gewicht	Excluding Lens 44.5 kg / 98.1 lbs
Verzendingsafmetingen	Excluding Lens 720 x 910 x 630 mm 28.4 x 35.8 x 24.8 in.
Verzendgewicht	Excluding Lens 55kg / 121.3 lbs
Opslagtemperatuur	-20 to 60 °C
Vochtigheid bij opslag	10 to 90% (relative humidity)
Standaardaccessoires	Power Cord, Remote Control
24/7 operation	This projector is designed and warranted for heavy duty 24/7 operation. Specific measures and design considerations have been made in order for it to comply with stringent requirements in challenging applications.
Certificeringen	CE, FCC Class A and cCSAus
Veiligheidsvereisten	This projector is Risk Group 2 (RG2) according to IEC EN 62471-5.  This projector may become Risk Group 3 (RG3) when an interchangeable lens with throw ratio greater than 3.15 is installed.  For Northern America, installation requirements according to Risk group 3 (RG3) must be followed when interchangeable lens with throw ratio greater than 2.33 is installed.  Refer to the installation manual for further information.
Garantie	Limited 3 years parts and labor Extendable up to 5 years
*	Firmware upgradable Please contact an authorized Barco representative for details

**Laatst bijgewerkt: 09 Jul 2024**

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer [www.barco.com](http://www.barco.com) voor de nieuwste specificaties.

[www.barco.com](http://www.barco.com)**BARCO**