

OverView cPR67 (Atlas CS4)

67" Display Wall system integrating 3-panel Poly-Silicon LCD technology with SXGA resolution.



技术规格

OVERVIEW CPR67 (ATLAS CS4)

一般规格

分辨率	SXGA
宽高比	5:4
颜色	16.7 millions
灯泡	<ul style="list-style-type: none">· 100 Watt lamp· operation time 8,000 hours (average)
电源	95-230 VAC ± 10%, 50-60 Hz
电源	220 W
亮度	110 cd/m ² 32 ftL
亮度	500 lumens
对比度	350:1
亮度均匀性	> 95%
尺寸结构	<ul style="list-style-type: none">· Diagonal 67"· Width 1335 mm / 52.56 in.· Height 1068 mm / 42.05 in.· Footprint 798 mm / 31.4 in.· Depth 942 mm / 37.1 in.· Socket heighth min 492 mm / 19.4 in.
运行环境	<ul style="list-style-type: none">· Operating temperature: 17 °C -27 °C or 62 °F -80 °F· Humidity: recommended 40% -60%, non condensing Typical for stiched screens.
屏幕	<ul style="list-style-type: none">· high gain screens for high brightness and high contrast black screens for wide viewing angles· other screens on request

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。