

EP10

The Barco EP10 –superb quality,outstanding performance,installation flexibility and ease of operation combined in one cost efficient solution for almost any application in Exhibition or Post Production.



Spécifications techniques

EP10

Spécifications générales

Technologie	3 x 0.8" chip, DLP™
Résolution	1280 x 720
Taux de contraste	16 x 9
Luminosité	3000 ANSI Lumens
Contraste	1200 : 1
Couleurs	4.4 m colors
Taille maximale d'écran (diagonale)	10m (32ft)
Dimensions	282 x 605 x 694 mm (HxWxD)
Poids	25 kg
Consommation électrique	1000 W
Niveau sonore	42 dBA
Entrées	Native DVI, SDI, Component, S-Video, Composite Optional SDI
Lentilles anamorphiques	Not required
Lampe	Size 2 x 250W UHP
Contrôle	RS232 / 422
Caractéristiques particulières	16:9 DLP chip format Dual lamp operation

Créé le : 09 Jul 2024

© 2024 Barco nv. Tous droits réservés. La reproduction partielle ou intégrale sans autorisation écrite préalable est interdite. Les noms de marques ou de produits sont des marques commerciales, des marques déposées ou des appellations commerciales appartenant à leurs détenteurs respectifs. Pour des raisons d'innovation continue, les informations et les caractéristiques techniques sont susceptibles d'être modifiées sans préavis. Veuillez consulter www.barco.com pour les dernières spécifications.