

NGC-102

2-slot chassis



Product specifications**NGC-102****General specifications**

Rack mount	19" rackmount housing; 2U height
Dimensions	494.8 x 450.0 x 87.1 mm (19.48 x 17.72 x 3.47 inch) without handles
Weight	11.5 kg with PSU (without boards)
Hot swappable	All active components
Noise Level	45 dBA at 25°C, 64 dBA at 40°C
Input power	2x300 W, redundant power supply
Input voltage	90-264VAC
Input frequency	47-63Hz
Inrush current limiting	2x40A (max) (redundant power supply)
EMI	EMI input filter Class B
PCF	0.95 (power factor corrected)
Efficiency	80% at typical load
Operating temperature	0° to 40°C
Heat dissipation	900 BTU/h
Shelf management	Active fan speed regulation, System health monitoring, SNMP agent, Browser based access to system statistics
Chassis	2,746,000 hours
Hot-swap Power supply	100,000 hours
Hot-swap Fan module	225,000 hours
Safety Regulations	CE, UL and CCC certified

Last updated: 08 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.