


FLM-HD20

20,000 lumens, 1080p HD, 3-chip DLP projector



Barco's FLM-HD20 is an ultra-bright, durable projector with full HD picture-in-picture capabilities. It is a perfect fit for any large venue that requires extra brightness to show clear, crisp images in a luminous environment.

Powerful projection for large venues

Thanks to the FLM-HD20's 20,000 lumens light output, it can display widescreen, high-contrast images of superior quality even in venues with lots of ambient light. Through its superior video processing and picture-in-picture capabilities, you can make your presentations more interactive and energizing without the need for extra peripherals.

Most silent projector in its class

The FLM-HD20's liquid cooling technology cuts noise levels to a minimum, making it one of the most silent projectors in its class. The FLM is also equipped with a sealed optical engine that prevents dust, smoke or other environmental contamination from affecting its image quality.

Ultra-bright and stunning images

- High contrast 3-chip DLP™ engine
- True native HD resolution
- 20,000 center lumens
- Contrast ratio of 1,800:1

Low total cost of ownership

- Sealed engine with constant image quality over time
- Projector designed for high resistance against external contamination

- Extended lamp warranty (750 hours)
- Extremely good lamp maintenance (typical 1,000 hrs)
- TLD+HD lens range that is fully compatible with the Barco's HDX projector series

Built for demanding rental & staging applications

- Fully sealed optics
- Easy to set up, install, service and transport
- Removable lamp house, power supply & electronics
- Low video delay (broadcast live events)
- Universal lamp house for all FLM projectors

Fit for any widescreen & creative application

- High brightness projection at 20,000 center lumens
- "High-Contrast Mode" (2,400:1) feature enables you to make a trade-off between brightness and contrast, depending on your application.
- Low video delay, very important when broadcasting live events
- Ultimate solution for projection on multiple screens and special surfaces

Projector Toolset software

The FLM comes with standard "Projector Toolset" software, offering basic control, diagnostics and other features (e.g. a lens program). Additional software plug-ins can be offered as an option delivering added functionality for multi-screen applications, advanced settings control, etc. A user friendly GUI (Graphical User Interface) ensures easy control.

Product specificaties

FLM-HD20

General specifications

Type projector	Full HD 3-chip DLP digital projector
Technologie	0.95" DMD™ x3
Resolutie	1,920 x 1,080
Helderheid	20,000 center lumens / 19,000 ANSI lumens
Contrastverhouding	2,100:1 / 2,700:1 (high contrast mode)
Helderheidsuniformiteit	90%
Beeldverhouding	16:9
ScenergiX	Horizontal and vertical edge blending
Type lens	TLD+
Lenzen	0.73:1 ; 1.2:1 ; 1.25-1.6:1 ; 1.5-2.0:1 ; 2.0-2.8:1 ; 2.8-4.5:1 ; 4.5-7.5:1 ; 7.5-11.5:1
Optische lensverschuiving	Vertical: -10% to +110% ; Horizontal: -50% to +50% (on zoom lenses)
Kleurcorrectie	P7
Lampen	3kW xenon
Levensduur lamp	1,000 hours
Transport met lamp	Yes
Lampbehuizing, snelle vervanging	Yes
Lampvervanging door klant	Yes
Lampgarantie (vervanging op locatie/in de fabriek)	90 days, 500 hours / pro rata 750 hours
Verzegelde DLP™-kern	Standard
Optische dowser	Standard
Picture-in-Picture	Two sources simultaneously
Oriëntatie	table -ceiling -side (portrait) -vertical
DMX 512	Optional
WARP	Preset values + custom
Geïntegreerde webserver	N/A
CLU (constante lichtuitvoer)	Standard
Geschikt voor 3D (optioneel)	Passive Infitec
Ingangen	DVI(HDCP); 5-BNC RGBHV (RGBS/RGsB, YUV CS/SOY, Composite video, S-Video); SDI/HDSDI
Optionele ingangen	DVI(HDCP); 5-BNC RGBHV (RGBS/RGsB, YUV CS/SOY, Composite video, S-Video); SDI/HDSDI
Invoerresoluties	From NTSC up to UXGA (1,600 x 1,200) incl. HD (1,920 x 1,080)
Max. pixelklok	165 MHz
Softwaretools	Projector Toolset
Controle	XLR wired + IR, RS232
Netwerkverbinding	10/100 base-T, RJ-45 connection
Voedingsvereisten	220-240V / 50-60Hz
Max. energieverbruik	3700W
Geluidsniveau (standaard bij 25°C/77°F)	58dB(A)
Operationele omgevingstemperatuur	0-40°C / 32°-104°F
Operationele vochtigheid	0-80% (non condens)
Dissipatie BTU	max 12,625 BTU/h
Afmetingen (B x L x H)	707 x 1,025 x 548mm / 27.83 x 40.35 x 21.57 inches
Gewicht	99kg (218.25lbs)
Verzendingsafmetingen	(LxWxH) 1,200 x 980 x 760 mm / 47.24 x 38.58 x 29.92 inches
Verzendgewicht af fabriek	151kg (333lbs)
Standaardaccessoires	Power cord, wireless/XLR wired rugged remote control
Certificeringen	Compliant with UL1950 and EN60950 complies with FCC rules & regulations, part 15 Class A and CE EN55022 Class A, RoHS
Garantie	2 years

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

www.barco.com

BARCO