

CRPN-62B

5,500 lumens, Panorama, single-chip DLP projector



- Razor-sharp images with vibrant colors
- Panoramic canvas
- Compact design
- 24/7 reliability

*Only available at selected distributors

The CRPN-62B is the perfect solution for wide-screen projection in high-end meeting rooms, boardrooms and collaboration rooms that require multi-windowing features.

Better collaboration

Having an efficient and detailed view of complex data sets is paramount in order to make the right decisions. Thanks to the CRPN-62B's unique Panorama (2,560 x 1,080) resolution and 21:9 aspect ratio, you can easily share highly detailed information in a side-by-side manner. Did you know that showing more data on screen simultaneously has a documented effect on work efficiency?* Allowing multiple participants to be on-screen simultaneously and share various types of content, the CRPN-62B enables better collaboration.

High-quality images

With its 5,500 lumens brightness level, the CRPN-62B provides stable, uniform and high-contrast images, that enable you to concentrate better and focus on what matters most in meetings: the agenda. And thanks to its low noise level, working in an environment with front projection has never been less distracting.

Built to last

The CRPN-62B features a filter-free design and reliable DLP® technology for unmatched picture accuracy and low total cost of ownership. Designed for unlimited use, it also comes with a three-year warranty, for true peace of mind.

Product specificaties

CRPN-62B

General specifications	
Type projector	Single-chip DLP projector
Technologie	LVDC DMD™ with DarkChip3™
Resolutie	2,560 x 1,080 (Panorama)
Helderheid	5,500 ANSI lumens
Contrastverhouding	6,500:1
Helderheidsuniformiteit	>90%
Beeldverhouding	21:9
Type lens	All pure glass lenses
Lenzen	wide angle lens EN42 (0.8:1), ultra wide zoom lens EN46 (0.8-1.21:1), wide angle lens EN43 (1.2-1.7:1), standard zoom EN41 (1.7-2.5:1), long throw zoom EN44 (2.50-4.60 :1), ultra wide fixed EN47 (0.65 : 1)
Optische lensverschuiving	Vertical: -222% to +222%; horizontal: -78% to +78% (on zoom lenses)
Kleurcorrectie	RealColor™
Lampen	2 x 300W UHP Vidi
Levensduur lamp	Up to 2,000 hours (full power) / Up to 2,500 hours (eco mode)
Lampbehuizing, snelle vervanging	yes
Lampgarantie	500 hours or 90 days
Verzegelde DLP™-kern	Yes
Oriëntatie	table -ceiling
Ingangen	2 x DVI-I; 2 x HDMI 1.3a; 2 x VGA; Video inputs; 1 x component; 1 x S-video
Invoerresoluties	Up to 2,560 x 1,600 pixels input on all models. Output resolution depends on native resolution; HDTV (1080p, 1080i, 720p); EDTV (576p, 480p); SDTV (576i, 480i); NTSC, PAL, SECAM; progressive scan
Software tools	Projector Toolset, ProNet
Controle	1 x RJ-45 TCP/IP; 1 x 9-pin D-SUB RS232; 2 x 12V programmable trigger (3.5mm mini jack); 1 x Wired Remote 3.5mm mini jack; 2 x USB
Netwerkverbinding	10/100 base-T, RJ-45 connection
Voedingsvereisten	100-240V / 50-60Hz
Energieverbruik	912W
Geluidsniveau	34 dB
Operationele omgevingstemperatuur	10-40°C / 50°-104°F
Operationele vochtigheid	20-80% RH
Dissipatie BTU	max 3,109 BTU/h
Afmetingen (B x L x H)	510 x 376 x 233 mm / 20.08 x 14.80 x 9.17 inches
Gewicht	12.7 kg (28.0 lbs)
Standaardaccessoires	Power cord, wireless remote control
Certificeringen	Compliant with FCC, part 15 Class A and CCC, cCSAus, cUL, UL and CE
Garantie	Limited 3 years parts and labor. Extendable up to 5.

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

