


VRWF-3200

Network-centric VR workroom display for stereoscopic data analysis and decision-making



Product specificaties

VRWF-3200

General specifications

Projector	2x iCon H600, side-by-side ceiling mounted
Resolutie	HDTV (1920 x 1080 pixels)
Hoogte actief scherm	1.8m (70")
Breedte actief scherm	3.2m (125")
Lens	QHD 1.4 -2.1
Ingangen	Standard: ■ 2x Composite Video (BNC) ■ 2x S-Video (4-pin mini-DIN) ■ 1x DVI ■ 1x VGA (D15 connector) ■ 2x 5-BNCs capable of connecting ■ Video over IP ■ Audio: microphone and line-in (mini-jacks) Optional: ■ Extension with extra video input (Composite and S-Video) ■ Extension to SDI and HD-SDI
Netwerkverbinding	The integrated display server allows easy integration in a network infrastructure.
Picture-in-Picture	Up to 4 external sources
Controle	The VRWF-3200 workroom display can be powered up or down by means of RS232.

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

www.barco.com

BARCO