

D-Cine Premiere DP100

2k Digital Cinema projector for large screens up to 20m (65.6ft)



Spécifications techniques

D-CINE PREMIERE DP100

Spécifications générales

Luminosité	22,000 cinema lumens
Digital MicroMirror Device™ (matrice de micro-miroirs numériques)	3 x 1.2" dark metal type Advanced DLP Cinema™ signal processing: CineCanvas™ image management, CinePalette™ color management, CineBlack™ contrast management and CineLink™ security management
Résolution native	2048 x 1080
Boîtier	Hermetically sealed DMD™ and optical assembly
Largeur de l'écran	Screen width (screen gain 1:8) @ 14ftL: 25m -82ft adjustable light output CLO software
Montage	Standing on pedestal, including caster & wheels Up to 15 degrees tilt on pedestal
Lampe	1.5k to 7k Xenon arc lamp sizes Compatible with standard and high performance lamp types
Taux de contraste	2000:1
Entrées vidéo numériques	2 x SMPTE 292M inputs 2 x DVI input both selectable as single or as dual link
Lentilles primaires	M25 1.25 -1.45:1 / M25 1.45 -1.8:1 / M25 1.8 -2.2:1 / M25 2.2 -3.0:1 zoom and M25 3.0 -4.3:1
Diagnostics du projecteur	Via touch screen Via D-Cine Communicator control software (theater edition delivered standard on every product) Via SNMP agent
Alimentation électrique	3 x 400V + N or 3 x 220V version available max. 29,250 BTU/hr (with 6.5kW lamp)
Dimensions	projector head: 640(H) x 730(W) x 1186(D) mm / 24.2(H) x 28.7(W) x 46.7(D) inch projector head + pedestal: 1466(H) x 730(W) x 1252(D) mm / 57.7(H) x 28.7(W) x 49.3(D) inch
Poids	projector head + pedestal: approx. 205kg (452lb)
Options	- CLO -Constant Light Output control - Anamorphic lens fitting for 1.25:1 scope lens - Acsar 2 Alternative Content Input Processor - ImagePRO HD - SNMP agent (v3)
Référence	EU: R9010111 US: R9010118

Crée le : 09 Jul 2024

© 2024 Barco nv. Tous droits réservés. La reproduction partielle ou intégrale sans autorisation écrite préalable est interdite. Les noms de marques ou de produits sont des marques commerciales, des marques déposées ou des appellations commerciales appartenant à leurs détenteurs respectifs. Pour des raisons d'innovation continue, les informations et les caractéristiques techniques sont susceptibles d'être modifiées sans préavis. Veuillez consulter www.barco.com pour les dernières spécifications.