

NGS-D320 FLEX Pro

Compact 4K dual channel H.264 & V2D Encoder



- **Superb Visual Experience**
- **Simple Integration**
- **No Adjustment Needed**
- **Performance**
- **Flexible switching between the H264 or V2D protocol**
- **Dual channel support**
- **Part of the TFN and OpSpace Product families**

The NGS-D320 FLEX Pro is a versatile and powerful networked H.264 and V2D encoder. Its elegant design, small form factor and silent operation allows the device to be used in any situation, both in office environments and in 24/7 mission critical applications.

Due to its versatility, the NGS-D320 FLEX Pro can be configured at runtime as an encoder, both for DVI, HDMI™ and DisplayPort content, with or without audio and USB KB/M. Unique in the market, it supports 2 types of streaming protocols (H264 and V2D) over 1 or 2 streaming channels in a flexible way, enabling the best possible user experience for a wide variety of use-cases. The combination of these functions, with integrated keyboard and mouse control in a single unit, is ideal to create a seamless environment for application sharing, simulation and training.

Key features:

- **Superb Visual Experience:** The NGS-D320 FLEX Pro comes with Barco's latest dual channel image processing engine, which provides the best scaling and color space conversion algorithms on the market today. When distributing graphics, the encoder preserves even the smallest details, making it suitable to encode images like spreadsheets or single pixel line diagrams.
- **Simple Integration:** The device automatically starts streaming whenever a valid input signal is connected. The stream is automatically set up using the most optimal settings based on input resolution and bandwidth. In addition, the discovery page of the web interface gives an overview of all available devices in the network, making system configuration easy. The device is validated to work in Barco Transform N 3.3 or higher and



- **Simple Integration:** The device automatically starts streaming whenever a valid input signal is connected. The stream is automatically set up using the most optimal settings based on input resolution and bandwidth. In addition, the discovery page of the web interface gives an overview of all available devices in the network, making system configuration easy. The device is validated to work in Barco Transform N 3.3 or higher and OpSpace 1.4 or higher.
- **No Adjustment Needed:** With automatic EDID management, the best experience in distributing graphics and video over IP is guaranteed. Fiddling with displays to get a good picture is thus unnecessary. Switching from one source to another is fluent and does not require the display to re-sync to the new signal. The decoder can also both upscale and downscale to match the preferred display settings.
- **Performance:** The NGS-D320 FLEX Pro comes with a dual link DVI, an HDMI™ 1.4 and a DisplayPort 1.1a input out of which 2 can be used at the same time. All inputs support resolutions up to 4096 x 2160 (DCI) and feature active pass-through connectivity. Encoding using H264 or V2D in full frame rate or lower frame rates is possible, allowing you to define the most optimal quality/bandwidth balance. The encoder latency is below 40ms enabling the foundation for a low end-to-end latency in a broad variety of systems.

Product specificaties**NGS-D320 FLEX PRO**

Number of inputs and outputs	
Audio	1 3.5mm jack stereo line level in & line out 1 3.5mm jack mono mic in & stereo headphones out (combined)
USB	3 Type A connectors, 1 Micro-B connector
Netwerk	RJ45 (redundant 1Gb Ethernet copper)
Video	1 Dual Link DVI & 1 DisplayPort 1.1a & 1 HDMI 1.4 input 1 Dual Link DVI & 1 DisplayPort 1.2 & 1 HDMI 1.4 output Flexible Loop Through Maximum input bandwidth of 330Mhz
Network interfaces	
Ethernet	2x 1GbE full duplex
IP-adressering	DHCP, link local, fixed IP
Protocollen	Unicast, Multicast (IGMP v3), RTP, RTSP
RTSP-sessies	Multicast: maximum 12 simultaneous RTSP session per channel Unicast : maximum 2 simultaneous RTSP session per channel
Detectie	Zeroconf, SAP (RFC 2974)
Management interfaces	
Firmware-upgrade	HTTPS Web interface, USB Storage Device
Alleenstaand	HTTPS Web interface
Advanced features	
Beeldverwerking	Color space conversion, scaling, frame rate reduction
Automatische verkleining	Y (Adjust to profile)
Extern toetsenbord en muis	Supported (native keymap)
General specifications	
Afmetingen	38 mm H x 170 mm W x 170 mm D 1.5" H x 6.7" W x 6.7" (+/-2mm / 0.1")
Gewicht	1 ± 0.01 kg (2.20 lbs)
Vermogen	Typical 35W, maximum 48W
Voeding	12VDC, 100-240VAC 60W, external locking power
Bedrijfstemperatuur	0°C to 40°C (32°F to 104°F)
Opslagtemperatuur	-20°C to 70°C (-4°F to 158°F)
Geluidsniveau	Typical 32dBA at 20°C
Montage	Optional VESA adapter plate or 1U rack mount for 2 devices

Product specificaties**NGS-D320 FLEX PRO**

Certification	
EMC	CE, FCC Part 15 Class A, ICES-003
Veiligheid	UL/ cUL/ EN/ IEC 60950-1 CB report
Wettelijke naam	NGS-D320
Packaging characteristics	
Afmetingen (verpakt)	382mmx273mmx85mm 15,04"x10,75"x3,35"
Gewicht (verpakt)	2.2 kg 4.8 lbs
NGS-D320 Pro	
Aantal kanalen	Up to 2
Aantal streams	Up to 2
Grafisch	640x480 -2560x1600 24-60Hz 640x480 -4096x2160 24-30Hz
Audio	uncompressed
Codec	Video: H.264 up to level 5.1 and/or V2D -60fps: up to 1920x1200 (2x) -30fps: up to 2560x1600 (2x) -60fps: up to 2560x1600 (1x) -30fps: up to 4096x2160 (1x) (version 2.1 or higher)
Bandbreedte	Video: H.264 384kbps – 24Mbps V2D 25Mbps – 200Mbps Audio: uncompressed
Latentie encoder-decoder end-to-end	80-200ms (typical 100ms)
Opstarttijd	15s

Laatst bijgewerkt: 17 May 2024

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.