

# FS40-WU

Rock-solid and powerful WUXGA LED projector for NVG training

- **Night Vision Goggles stimulation**
- **True solid state and ruggedized**
- **Bright LEDs with exceptional color fidelity**
- **100-0% LED dimming for training at any time**
- **Barco Pulse software ensures lowest latency**

The FS40-WU is a true solid state projector, using the latest in HLD and LED illumination technology. It combines amazing visual performance and extreme reliability with a low TCO.

This dedicated IR projector allows for full individual control of visual and IR intensity to stimulate NVGs with IR transmission at 740nm. Dual iris and optical filters ensure better contrast and higher black levels. Even in the most demanding environments, the FS40 delivers a vision to trust.

### **Extreme reliability in all situations**

Thanks to the Single Step Processing (SSP<sup>®</sup>) technology in Barco Pulse the FS40 delivers high resolution images faster and at lower latency than any other competing technology. No matter whether pitching, rolling, or bouncing, for training in air, at sea, or on land, the Barco FS40 is a true solid state projector with no moving parts or lamps. Its solid magnesium front and baseplate act as mounting plates. Coupled with an array of mounting points in the front and on the top, they make this projector solid as rock and perfectly suited for use on motion platforms

### **Lowest TCO**

The FS40 uses a proven DLP<sup>®</sup> sealed optical engine and latest solid state HLD LED illumination.

Simulator operators can benefit from reduced Total Cost of Ownership (TCO) with extended maintenance cycles and no lamp changes or color adjustments for up to 50,000 hrs. Barco Constant Light Output (CLO) functionality ensures total predictability in linear brightness performance over the life of the projector. Additional protection is available when using new intelligent high-efficiency air filters for installations in dusty and polluted environments.