

Barco Kroma MKII



Featuring our 2nd generation LED illumination system, Barco Kroma MKII produces a stunning, wide and extremely consistent color gamut and a rich, vibrant color rendition. With an unmatched 100,000 hour life expectancy, 13 lens options and close to unlimited installation flexibility, Barco Kroma MKII delivers the ultimate in image quality for smaller dedicated home cinema rooms.

技术规格

BARCO KROMA MKII

一般规格

| | |
|-----------|---|
| 投影机类型 | 2nd Generation Solid State LED DLP® projector. |
| 光输出 | up to 900 lumens |
| 对比度 | Up to 8,000 : 1 (Infinite contrast and total black with Dynamic Black enabled) |
| 透镜范围 | 0.61, 0.75-1.13, 1.12-1.58, 1.58-2.33, 2.37-3.79, 3.8-6.5 : 1 |
| 光学镜片移动 | adjustable: vertical and horizontal, depending on lenses |
| 灯 | LED |
| 灯泡寿命 (典型) | LED Up to 100,000 hours |
| 封装DLP™内核 | standard |
| 兼容性 | "HDTV (1080p, 1080i, 720p), EDTV (576p, 480p), SDTV (576i, 480i), NTSC, PAL, SECAM, progressive scan" |
| 3D | "active eyewear (optional), 2x optix cinemascope(stacked): INFITEC EX® 3D and Active Stereo IR, RF models, DLPLink™" |
| 输入 | "2 x DVI-I, 2 x HDMI 1.3a, 2 x VGA 1 x Component, 1 x S-video" |
| 控制 | "1 x RJ-45 TCP/IP, 1 x 9-pin D-SUB RS232, 2 x 12V programmable trigger (3.5mm mini jack), 1 x Wired Remote 3.5mm mini jack, 2 x USB AMX Device Discovery, Crestron Certified Partner" |
| 电源 | 6.5A, 200-240V, 50-60Hz |
| 功率消耗 | "Certified rating: 8.4A, ~100-240V, 50-60Hz Typical consumption: Max 325W@100V, ~2.7A, 50Hz; ~1.2A, 240V, 50Hz" |
| 工作温度 | 10 -40 °C |
| 操作湿度 无冷凝 | 20 -80% RH |
| 消散 BTU | less than 1,100 |
| 安装 | table top, ceiling mount, straight down or up. |
| 尺寸(宽x长x高) | 510 x 376 x 223 mm excluding lens |
| 净重 | 12.7 kg, shipping weight 20 kg |
| 装运尺寸 | 780 x 520 x 370 mm (WxHxD) |
| 机箱颜色 | black and white |
| 认证 | CCC, cCSAus, FCC Class A, cUL, UL and CE |
| 保修期 | "limited 3 years warranty. Up to five years extended warranty available. Conditions apply." |

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。