

EP10

The Barco EP10 –superb quality,outstanding performance, installation flexibility and ease of operation combined in one cost efficient solution for almost any application in Exhibition or Post Production.



技术规格

EP10

一般规格

技术	3 x 0.8" chip, DLP™
分辨率	1280 x 720
对比度	16 x 9
亮度	3000 ANSI Lumens
对比度	1200 : 1
颜色	4.4 m colors
更大屏幕尺寸(诊断)	10m (32ft)
尺寸	282 x 605 x 694 mm (HxWxD)
净重	25 kg
功率消耗	1000 W
噪音级别	42 dBA
输入	Native DVI, SDI, Component, S-Video, Composite Optional SDI
变形镜头	Not required
灯泡	Size 2 x 250W UHP
控制	RS232 / 422
特殊性能	16:9 DLP chip format Dual lamp operation

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可, 禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新, 信息和技术规格如有变更, 恕不另行通知。请查看www.barco.com.cn以了解最新规格。