


D310



- -
3 to 2 and 2 to 2 Pull Down (patented Motion Picture Processing)-Time Based Correction-Video Equalizing (3-Band)-
Dynamic Image Stabilization-
Digital Brightness/Saturation Control-Scaler/Compressor-
Automatic RGB Matrix Selection-
Analytical Contrast Rendering (Stretch to SubBlack,
Gamma (RGB))-Luminance Tracking-
Dynamic Sample Weight Distribution

技术规格

D310

一般规格

兼容性

- All video sources (PAL, SECAM, NTSC 3.58, NTSC 4.43 in Composite, S-VHS, RGB or Component format)
- All computer graphics up to SVGA (800 x 600)
- All Macintosh computers (640 x 480)
- Pannellink loop through data signal

输入

- Two Composite Video inputs on BNC connectors
- Two S-video inputs on 4 pin mini-Din connectors
- Once Component Video input (R-Y, B-Y, Y, sync) on 4 x BNC connectors
- One RGBs or RGSB input on 4 x BNC connectors
- One Pannellink input

输出

- Pannellink data output
- Long/Short Distance digital link
- RGBs or RGSB output on HD15 connector (monitor)
- RS 232 loop-through communication port on D9 male & female connectors
- RS 485 Phoenix connectors for AX Link

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看www.barco.com.cn以了解最新规格。