


Njord Cinemascope

Njord Cinemascope has a pleasing calm uniform image and is designed for large screens or high ambient light environments.



- Theater & Media Room Series
- 5K UHD Resolution (5,120 x 2,160)
- 3-Chip DLP
- Up to 9,000 ANSI Lumens

Njord Cinemascope inherits everything from Njord except the aspect ratio, Njord Cinemascope's high-capacity 2.37:1 aspect DLP engine. Its exceptional design allows a cinemascope film to be shown without requiring an anamorphic lens. The light source and optical engine are completely redesigned, made smaller, more efficient, and most importantly optimized for perfect cinematic colors compared to the older model Wodan.

Single Step Processing SSP™

Pulse is a hardware and software based platform that simplifies the signal allowing it to transmit from source to screen much faster and more efficiently. We use an advanced image processing technique to display the image on the screen without any artefacts and with the lowest possible processing lag (<20ms with all image processing), this is made possible by our Single Step Processing (SSP™).

State of the art electronics

All new Pulse electronics have been designed to process 4K with HDMI 2.0a and HDCP 2.2 and the optical engine utilises the very latest 0.9" DMD DLP chipset, delivering 5,120 x 2,160 pixels to screen. Njord CS also features HDR, motorised lenses and Barco's unique RealColor processing, enables simple and accurate calibration to any desired color standard or white point.

Building Blocks

Njord Cinemascope offers 5K UHD resolution (5,120 x 2,160) for superb image quality. Thanks to its modular design of only five building blocks, Njord CS is easy to service. Njord CS is the most compact and rugged cinemascope projector offering 9,000 lumens light output currently available.

Laser Light Source

Lasers last longer than traditional projector lamps, are not as fragile and offer nearly instant on/off.

Product specificaties**NJORD CINEMASCOPE**

General specifications	
Type projector	Three chip DLP
Technologie	3 x 0.90" DMD™ with sealed core
Resolutie	5120 x 2,160 (5K UHD)
Beeldverhouding	2.37:1 (CinemaScope)
Lichtbron	Laser phosphor
Levensduur lichtbron	Up to 20,000
Lichtuitvoer	Up to 9,000 ANSI Lumens Dimable to 4,000 lumens NOTE: Up to 6,940 ANSI Lumens @ 110v
CLU (constante lichtuitvoer)	Yes
Contrastverhouding	20,000:1 (with DynaBlack enabled) 2,000:1 Sequential 600:1 ANSI
Helderheidsuniformiteit	>90%
Lensbereik	(R9801661) -TLD+ (0.41:1) -90 Degree Lens (R9862001) -TLD+ (0.73 - 0.94:1) -90 Degree Lens (R9801414) -TLD+ (0.92 - 1.33:1) (R9862005) -TLD+ (1.24 - 1.56:1) (R9862010) -TLD+ (1.49 - 2.02:1) * (R9862020) -TLD+ (2.01 - 2.76:1) * (R9862030) -TLD+ (2.69 - 4.41:1) * (R9862040) -TLD+ (4.37 - 7.35:1) * (R9829997) -TLD+ (6.95 - 10.83:1) * Standard Lens Option(s)
Optische lensverschuiving	Up to 97% shift up, 76% down, & up to 28% horizontal lens shift (depending on lens selection) Visit the Barco Residential Lens Calculator for further information Download Lens & Airflow Data Here
Optische dowser	Yes
Kleurcorrectie	P7 RealColor™
Kleurenspectrum	Up to DCI (P3)
Beeldverwerking	Embedded Warp & Blend Engine
WARP	4-Corner Warp & Bow Correction via Warp Engine
Oriëntatie	360° Rotation
Netwerkverbinding	10/100 Ethernet via RJ45 connection
Geïntegreerde webserver	Yes
Diagnose	via Prospector web interface
HDR	HDR10
3D	Active Stereoscopic 3D Additional hardware required please contact an authorized Barco representative for details

Product specificaties**NJORD CINEMASCOPE**

Ingangen	1 x HDMI 2.0 (HDCP 2.2) 2 x HDBaseT (HDCP 1.4 -9Gbps only) 1 x Display Port 1.2 Quad 3G / 12G SDI / BarcoLink 1 x RJ45 Ethernet 1 x RS232 1 x USB 2 x DMX (1 x Input / 1 x Output) 1 x XLR for Wired Remote 2 x 3D Sync (1 x Input / 1 x Output) Optional Upgrade: Quad DP1.2
Invoerresoluties	HDMI: Up to 4,096 x 2,160 @ 24/25/30/50/60Hz DisplayPort (Single Input): Up to 4,096 x 2,160 @ 24/30/50/60Hz via Optional Quad DP1.2 Input Card DisplayPort (Layout Mode: 2 x 2) *: Up to 1,920 x 1,080 @ 120Hz Up to 2,048 x 1,080 @ 120Hz DisplayPort (Layout Mode: 4 x 1) *: Up to 960 x 2,160 @ 120Hz * Specialist GFX cards may be required
Latentie	TBD
Controle	IR, RS232, IP, 12v Trigger Driver modules available for: Crestron, Control4, RTI & Savant WiFi (Optional), XLR Wired Remote, GSM (Optional)
Voedingsvereisten	110 -130V / 200 -240V / 50 -60Hz
Energieverbruik	110V: 1,347W Max, measured in 20-25°C / 68-77°F 230V: 1720W Max 20-25°C / 68-77°F Power consumption will increase if ambient temperatures increases above 25°C / 77°F
Geluidsniveau (standaard bij 25°C/77°F)	46 dB(A)
Bedrijfstemperatuur	0 to 40 °C at Sea Level Optimal Set Point: 20 °C
Operationele vochtigheid	0 to 80% (relative humidity)
BTU/uur	Max. 5,875 BTU/h @ 200 -240V Max. 4,599 BTU/h @ 110 -130V
Luchtstroomvereisten	Air Inlet (from Rear w/Feet Down): Front / Top / Right Exhaust (from Rear w/Feet Down): Rear Clearance Requirements: Front: 40cm Left: 1cm Right: 40cm Rear: 40cm Top: 40cm

Product specificaties**NJORD CINEMASCOPE**

Luchtuitstroom	152 ft ³ /min @ 25 °C 258 m ³ /hour @ 25 °C Download Lens & Airflow Data Here
Afmetingen (B x L x H)	Excluding Lens 540 x 725 x 355 mm 21.26 x 28.54 x 14 in.
Gewicht	Excluding Lens 48kg / 105bs
Verzendingsafmetingen (L x B x H)	Including Pallet -Excluding Lens (Packaged Separately) 850 x 665 x 613 mm 33.46 x 26.18 x 24.13 in.
Verzendgewicht	TBD
Standaardaccessoires	Power Cord / Remote Control
Certificeringen	CE, FCC Class A and cCSAus
Veiligheidsvereisten	This projector may become Risk Group 3 (RG3) when an interchangeable lens with throw ratio greater than 2.3 is installed. Refer to the installation manual for further information.
Garantie	Limited 3 years parts and labor Extendable up to 5 years
*	Firmware upgradable Please contact an authorized Barco representative for details

Laatst bijgewerkt: 22 Jun 2023

© 2018 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Vanwege voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Raadpleeg www.barco.com voor de meest recente specificaties.