

# SLite 22

Building on its longstanding expertise in video processing and large area display technology, the SLite LED display is Barco's solution to the need for large to ultra-large outdoor LED display installations.



## 技术规格

## SLITE 22

一般规格	
视觉分辨率	22,4 mm
物理分辨率	22,4 mm
亮度	6500 NIT 5000 NIT (calibrated @ 6500°K)
LED配置	1R, 1G, 1B
像素密度	1.991/m <sup>2</sup> (185/ft <sup>2</sup> ) 1.200/panel
水平观察角度	120° (min.50% brightness)
垂直视角	60° (min.50% brightness)
寿命	50 000 h (full white -half brightness)
功率消耗	maximum: 720 W / Tile average: 180 W / Tile
重量 / 层数	34 Kg / 75 lbs (excluding structure)
处理	color : 14 bit greyscale: 10 bit/color
颜色	4,4 trillion
刷新率	800 Hz minimum (PAL / NTSC)
温度范围	operating: -20 -40°C (-4 -104°F) storage: -20 -60°C (-4 -140°F)
湿度	operating: 10 -99% storage: 10 -99%
D320输入能力	S-Video -Composite -YUV -RGB -SDI -HDS DI -Data DVI up to UXGA
认证	UL -CE -TUV -FCC Class A
瓦状尺寸	width: 896mm (35.3") height: 672mm (26.5") depth: 249mm (9.8")

生成于: 09 Jul 2024

© 2024 巴可公司。保留所有权利。未经书面许可，禁止全部或部分复制。所有品牌名称和产品名称均为其各自持有者的商标、注册商标或商号。由于不断创新，信息和技术规格如有变更，恕不另行通知。请查看[www.barco.com.cn](http://www.barco.com.cn)以了解最新规格。