

OverView mP50

50" Display Wall system integrating 3-panel Poly-Silicon LCD technology with XGA resolution.



Product specifications

OVERVIEW MP50

General specifications

Resolution	XGA
Colors	16.7 millions Color management 30 bit/pixel
Lamp	<ul style="list-style-type: none">• 100W lamp• operation time typ. 8000 hours (average) integrated in a pre-adjusted lamp module, no re-adjustment after replacement
AC power	95-230 VAC \pm 10%, 50-60 Hz
Power	140 W
Luminance	250 cd/m ² 73 ftL
Brightness	600 lumens
Contrast	250:1
Brightness uniformity	> 95%
Dimensions structure	<ul style="list-style-type: none">• Diagonal 50"• Width 1,000 mm / 39.37 in.• Height 750 mm / 29.53 in.• Depth 568 mm / 22.36 in.• Weight 45 kg / 99.2 lbs
Environmental Compliance	operating temperature 0-40°C 30-105°F humidity max. 80% (non condensing)
Screens	HVA type 50" screen Width 1000 mm 39.37 in. Height 750 mm 29.53 in. Depth 96.5mm 2.77 in. Weight 9 kg 19.84 lbs

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.