

PDS-901 3G

Comutação de tela de alta qualidade para salas de diretoria ou salas de descanso



- Simple setup and operation
- Excellent price/performance ratio
- Simultaneous program output via DVI and analog connectors

The PDS series is designed to meet today's requirements for a high-quality, easy-to-use and fast seamless switcher with more digital inputs at an affordable price. Thanks to its straightforward setup and operation the PDS is a perfect fit for live events, boardrooms, hotel ballrooms, houses of worship, education and training facilities and fixed installations.

Program output

O PDS-901 3G possui quatro entradas DVI-I com suporte completo para HDCP 1.0, uma entrada 3G/HD/SD SDI e quatro entradas analógicas universais. All analog and DVI inputs support the EDID 1.3 specification. Users can capture and store up to three images that can be used as a LOGO source during the presentation. Built-in test patterns are also provided. O PDS-901 3G oferece saída de programa simultânea através dos conectores de DVI e analógicos. Ele também inclui uma saída SDI com suporte para taxas SD/HD/3G e BarcoLink para fácil conexão aos seus projetores Barco.

The PDS series won a Commercial Integrator BEST Award at InfoComm 2013.

Processing

- Fast source acquisition
- Fast and seamless switching
- Auxiliary control from Encore and ScreenPRO-II controllers
- Up to three LOGO stores/recall capability
- Low video delay
- Software download via USB

Inputs

- All resolutions from NTSC/PAL up to WUXGA including all HD resolutions
- EDID support for analog and DVI sources
- DVI, analog, SDI 3G/HD/SD and BarcoLink
- HDCP 1.0 support for all DVI sources

Preview and program outputs

- All progressive resolutions from 480p up to WUXGA/HD
- DVI, analog, SDI 3G/HD/SD and BarcoLink
- Full screen outputs and PIPs
- Dual PIP mode
- 9x2 Matrix mode
- Zoom and Stretch fit modes
- Supports HDCP compliant displays
- Built-in test patterns
- Independent resolutions for program and preview outputs

Mechanical

- Auto ranging power supply
- Slim 1 RU height
- Width: 19" rack

Especificações técnicas

PDS-901 3G

Especificações gerais

Sincronismo (Genlock)	N/D
Saída do programa	1 Saída do programa via HD-15, DVI ou 3G-SDI
Saídas auxiliares escaladas	N/D
Mixadores	1 mixer ou 2 pips
Entradas de vídeo	9 entradas fixas <ul style="list-style-type: none">4 x Analógicas via HD-15 (conector VGA)4 x Entradas DVI-I (suporte para analógico e DVI)1 x Entrada 3G SDI
Saídas de Vídeo	1x DVI, 1x HD-15 (VGA), 1x 3G SDI
Still stores	3
Efeitos em camada	Transições de mixagem e PIP para tela cheia
Multivisualizador	N/D
Capacidade de expansão	N/D
HDCP	Conformidade com HDCP
Controle	Ethernet RJ-45, computador autosense 10/100 mbps, tablet, smartphone via navegador web As funções de controle incluem: configuração de entrada da fonte, seleção de formato de saída, seleção de padrão de teste, seleção e controle de efeito de transição
Facilidade de manutenção	Conectores DVI substituíveis em campo
Dimensões	<ul style="list-style-type: none">Altura: 4,4 cm (1,75"), montagem em rack de 1 RULargura: 48,26 cm (19 in)Profundidade: 36,2 cm (14,25 in)
Peso	5,67 kg/12,5 lbs
Energia	Energia de entrada: 100 a 240 VCA 50/60 Hz 2 a máx
Temperatura ambiente	0 a 40 °C/32 a 104 °F
Umidade do Ambiente	0 a 95% sem condensação
Garantia	Três anos para peças e mão de obra

Gerada em: 09 Jul 2024

© 2024 Barco nv. Todos os direitos reservados. A reprodução total ou parcial sem permissão por escrito é proibida. Todos os nomes de marca e produto são marcas comerciais, marcas comerciais registradas ou nomes dos respectivos proprietários. Por causa da inovação contínua, as informações e as especificações técnicas estão sujeitas a alterações sem aviso prévio. Verifique www.barco.com para obter as especificações mais recentes.