

# High-performance Networked LCD video wall

Preconfigured control room package optimized for intensive networked applications



## Focus on high-performance networked applications

This bundle contains, next to 46" or 55" panels in a 2x2, 3x2 or 4x2 configuration, the TransForm NSD controller. This video wall controller is perfectly suited for more advanced functionality, such as collaboration via networked sources and high-performance video decoding. The main target industries for this package are traffic and security.

This bundle contains:

- Four, six or eight OverView NSL-4621 or OverView NSL-5521 panels
- TransForm NSD controller
- Chief wall mounts
- CMS software
- BCM software
- Keyboard (US type)
- Cables: - 20m KBM Extension - 20m Dual Link DVI-D cables -  
15m RS232 Serial Port cable - Power cords (EU/UK/US/CN)