


# TruePix TP1.5-E

1.5 mm pixel pitch, high-res indoor LED display for mid-brightness applications



- **Smart engineering guarantees truly seamless outcomes**
- **Smooth and efficient operations, 24/7**
- **Superb color accuracy, under all lighting conditions**
- **Reduced ecological footprint**
- **Up to 5 years of dedicated service and support**

TruePix TP1.5-E is Barco's new flagship indoor high-resolution LED platform. The 27.5" inch tiles, with a 16:9 aspect ratio, have a pixel pitch of only 1.5 mm. TruePix is designed for control room, corporate and broadcast visualization applications and supports both environments exposed to ambient light and controlled lighting environments.

## Truly seamless outcomes

TruePix sets a new standard for the LED video wall experience based on decades of experience. The solution brings content to life as intended and ensures predictable, truly seamless outcomes, by combining smart engineering and Infinipix® Gen2, the next generation of Infinipix®. Smooth and efficient operations are guaranteed 24/7, next to full peace of mind.

Barco TruePix' smart engineering introduces a unique mechanical concept for risk-free and precise installations, eliminating visual distortion. This unmatched seamlessness and flatness are achieved through guided module placement and self-leveling mounts. The next generation of Barco's proprietary Infinipix® processing – Infinipix® Gen2 – guarantees full image integrity at any brightness level, together with superb color accuracy. It flexibly and automatically supports any content need while reducing eye fatigue.

## Peace of mind at any time

Smooth and efficient operations are guaranteed 24/7 through uninterrupted data flows. Users can reduce the carbon footprint by using the EcoPower standby mode. Up to 5 years of dedicated service and support (ensuring a uniform viewing experience) and remote cloud-based video wall management, allow for peace of mind during the entire product lifetime.

**Product specifications****TRUEPIX TP1.5-E**

General specifications	
Pixel pitch	1.588
Pixel per tile	384x216 (HxV)
LED lifetime	100,000h (video -50% brightness)
Brightness	>600 nit
Internal processing	23 bit
Color depth	16 bit (281 trillion colors)
Shaders	Yes
Control	Infinipix® Gen2
Refresh rate	3,840 Hz
Frame rate	24 / 25 / 29.97 / 30 / 47.95 / 48 / 50 / 59.94 / 60 / 100 / 119.88 / 120 / 144 / 240 Hz
3D	3D supported
Hor. viewing angle	160° +/-5°
Vert. viewing angle	160° +/-5°
Brightness uniformity	>98%
Dimming	0-100%
Contrast	>7,000:1
Power consumption	702 W/m <sup>2</sup> 148 W/Tile (max) 234 W/m <sup>2</sup> 50 W/Tile(typ)
Heat dissipation	2,393 BTU/h/m <sup>2</sup> (max) 797 BTU/h/m <sup>2</sup> (typ)
Heat dissipation front/back	54%/46%
Operation power voltage	AC power: 100-240 V 50/60 Hz DC power: Input: 36-55Vdc 16A (max.) Output: 36-55Vdc 10.72A/36V (max.) or 12.55A/55V (max.)
Operational temperature	-10°C to +40°C / 14°F to 104°F For ceiling mounted installations: max temp +30°C/86°F
Operational humidity	10 -80%
IP rating	IPx0
Redundancy	Power: Optional Data: Inter-tile and signal loop redundancy embedded / N + N redundancy optional
HDR	HLG / HDR10 supported
Concave curvature	Up to 5° inter tile for standard and camera curved frame (7m radius) Up to 5° inner tile for standard and camera curved frame (3,5m radius)
Convex curvature	Up to 3° inter tile for standard curved frame (12m radius) Convex curving is not applicable for camera curved frame
Dimensions	(WxHxD) 609.92x343.08x71mm / 24.01"x13.5"x2.80"
Weight	7.5kg/tile (single PSU) 8 kg/tile (dual PSU)
Serviceability	Full front & full back service
Cable management	No external cabling
Installation	Self-leveling with surface tolerance compensation
Module replacement	Automated parallel motorized extraction
Module placement	Guided module placement
Ergonomics	SteadyView™ driver algorithm to reduce eye fatigue
Certifications	CE, UL, FCC class A, RoHS, WEEE, REACH, CCC, RCM
TAA Compliancy	Not available
Warranty	3 years
SmartCare / EssentialCare service offering	5 years

Last updated: 28 Aug 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check [www.barco.com](http://www.barco.com) for the latest specifications.