

Cineo22

ultra compact high end DLP® projector



The cineo22 comes standard in two different quality finishes; black and pearl white. The cineo22 completely redesigned optics present an image with higher resolution, lower dispersion and chromatic aberration, improved contrast, for greatly improved image quality.

Product specificaties

CINEO22

General specifications

Concept	single chip
3D-mogelijkheid	INFITEC EX@ 3D
Resolutie	1080p (1920 x 1080)
Helderheid	Up to 1400 lumens
Technologie	DLP® technology
Contrast	Up to 2500 : 1
Beeldverhouding	16:9 (1080p)
Beeldschermkleuren	30-bit
Latentie	1 frame
Grafische indelingen computer	up to 1080p
Horizontale scanfrequenties	15 -150 kHz
Verticale scanfrequenties	23.97, 24, 25, 30, 50, 60 fps
Videoformaten	EDTV (576p, 480p) HDTV (1080p, 1080i, 720p) SDTV (576i, 480i) NTSC, PAL, SECAM
Lenswerking	Focus, Shift and Manual zoom
Lenzen	Wide Angle <ul style="list-style-type: none">▪ Lens number:<ul style="list-style-type: none">EN17 / 503-0117-00▪ Focus range: 1.0 - 10.0 m▪ Throw ratio<ul style="list-style-type: none">• 0.92 : 1 (1080p) Ultra Wide Angle <ul style="list-style-type: none">▪ Lens number:<ul style="list-style-type: none">EN19 / 503-0110-00▪ Focus range: 0.7 - 5.0 m▪ Throw ratio<ul style="list-style-type: none">• 0.74 : 1 (1080p) Standard projection lens <ul style="list-style-type: none">▪ Lens number:<ul style="list-style-type: none">F3,5 / 503-0102-00▪ Focus range: 1.5 - 10.0 m▪ Throw ratio<ul style="list-style-type: none">• 1.60 - 2.21 : 1 (1080p)
Beeldbreedte	0.7 -2.5 m
Lichtbron	220W UHP
Levensduur lamp	Up to 2250 hours (Full power) Up to 3000 hours (Eco mode)
Computeringangen	1 x HDMI 1.3a 1 x VGA 1 x DVI-D
Video-ingang	1 x Composite 1 x S-video 1 x HDMI 1.3a 1 x DVI-D 1 x Component
Controlemogelijkheden	1 x RJ-45 TCP/IP 1 x 9-pin D-SUB RS232 1 x USB
Afmetingen	94 x 278 x 234 mm (WxHxD)
Gewicht	2.9 kg
Voedingsvereisten	3.0-1.3A, ~100-240V, 50-60Hz
Conformiteiten	CE, FCC Class A and cCSAus
Bedrijfstemperatuur	0 -40 °C
Opslagtemperatuur	-20 -60 °C
Vochtigheid in bedrijf	20 -90% RH
Vochtigheid bij opslag	20 -90% RH
Kleur	Black metallic
Garantie	3 years standard warranty, 500 hours or 90 days on lamp (whichever comes first) optional 3 years, 24/7 operation warranty, conditions apply.
MTBF	27,838 hours
BTU/uur	

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.