

TLD+ lens (1.14:1 WUXGA) (1.23:1 SXGA+)



Product specifications**TLD+ LENS (1.14:1 WUXGA) (1.23:1 SXGA+)**

General specifications	
Motorized Zoom	Not applicable
Motorized Focus	No
Throw Ratio	1.2 : 1
Lens Shift Horizontal	On SLM G5/G8 Left 64% 64% Right On SLM R6/R8 Left 59% 59% Right
Lens Shift Vertical	On SLM G5/G8 Up 100% 20% Down On SLM R6/R8 Up 84% 20% Down

Last updated: 15 Mar 2023

© 2018 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.