

iQ G400



기술 사양

IQ G400

일반 사양

광 출력	4,200 ANSI lumen
밝기 균일도	Brightness uniformity: >95 % for the total screen
LCD 패널	3 active matrix 1.3" diagonal XGA polysilicon LCD panels with Micro Lens Arrays and a resolution of 1024 x 768 pixels (aspect ratio 4:3). LCD panels are selected for a minimum of pixel defects.
해상도	1024 x 768 (native)
램프	2x 250 Watt UHP lamp, in lamp housing, pre-aligned for max. light output. Typical lifetime: 1000 h/lamp. 1000 hours in Dual Lamp Mode or max. 2000 hours/set in Single Lamp Mode.
렌즈	Fixed focal length lenses are available with a throw ratio of 0.85:1 (very short throw ratio, specially designed for rear screen on-axis projection) or 7.0:1 (long throw). Variable focus lenses with a throw distance of 1.3-1.8, 1.9-2.6, 3.0-6.0 times the screen width
스크린 크기	From 1-6 m/3-20 ft.
명암비율	>400 : 1 (full white/full black)
스캔 주파수	Horizontal 15 kHz -110 kHz Vertical 25 Hz -150 Hz
기능	• Advanced picture-in-picture • Seamless switching with effects • Standard cable basket • Standard light shutter • Advanced digital zoom
호환성	The iQ G400 is compatible with: • All current video sources (PAL, SECAM, NTSC) in Composite, S-VHS, Component or RGB formats • All currently proposed HDTV, extended and improved television standards (1080i, 720p) • All computer graphics formats from VGA, SVGA, XGA, SXGA to UXGA • Most Macintosh computers • Electronic workstations with a resolution up to 1600 x 1200 pixels at 75 Hz • Most computer sources with a pixel clock up to 160 MHz • DVI sources up to SXGA
입력	1x Configurable 5-Wire (BNC) for: Composite Video, S-Video, Component Video, RGBHV, RGBS, RGB. 1x Composite Video (BNC) (up to 7 Composite Video's when using all connectors on top input board) 1x S-Video (4-pin mini-DIN) (up to 3 S-Video's when combining BNC's) 1x VGA (D15 connector) 1x DVI (Digital Visual Interface)
크기(WxLxH)	Projector body with cable basket: 415 mm (Max W) x 195 mm (Max H) x 565 mm (Max D) Projector body without cable basket: 415 mm (Max W) x 195 mm (Max H) x 487 mm (Max D)
통신	1x D9 connectors for RS232 In/Out 1x spherical IR receiver
소음도	
AC 전원	Power factor pre-regulated SMPS, 90-254 VAC / 50-60Hz
전력 소비	Max 620 Watt
소비 전력	Max 2117 BTU/h
무게	Net weight: Body only 12.9 kg / 28.5 lbs. Shipping weight: • without lens max. 17.5 kg / 38.5 lbs. • with lens: max. 20 kg / 44 lbs.
렌즈범위	QVD Lenses Motorized V shift: -30% +120% For specific details per lens type: see lens product pages
무이음경계선(Seamless) 전환	Standard
네트워크 연결	Refer to IQ Pro G400

작성일: 09 Jul 2024

© 2024 Barco nv. All rights reserved. 서면 허가 없이 전체 또는 부분을 복제하는 것은 금지됩니다. 모든 브랜드명 및 제품명은 상표, 등록 상표 또는 해당 소유자의 상표입니다. 지속적인 혁신으로 인해 정보 및 기술 사양은 사전 고지 없이 변경될 수 있습니다. 최신 사양은 www.barco.com을(를) 확인하세요.