

MXRT-2100



Product specifications

MXRT-2100

General specifications

Bus	PCI Express® x16 native support
Bus clock speed	2.5 GHz
Bus width	16 Lanes
Power consumption	Computer supply of 350W or higher recommended
Operating system	<ul style="list-style-type: none">■ Windows 2000 Professional■ Windows XP Professional■ Windows XP x 64 Professional
Platforms	Intel and AMD architectures
Display configuration	Single or Dual Head, Portrait or Landscape
Graphics processor	ATI FireGL
Display memory	128 MB
Pixel clock rate	267 MHz
Look up table	32 bits in / 32 bits out
Electrical standard	Dual Link DVI complying with V1.0 specification
Supported resolutions / refresh rates	<ul style="list-style-type: none">■ 2048 x 1536 @ 50 Hz■ 1536 x 2048 @ 50 Hz
Operating temperature	0° to +55°C (32° to 131°F)
EMI	FCC, CE, BSMI, C-Tick, UL

Last updated: 09 Jul 2024

© 2024 Barco nv. All rights reserved. Reproduction in whole or in part without written permission is prohibited. All brand names and product names are trademarks, registered trademarks or tradenames of their respective holders. Due to continued innovation, information and technical specifications are subject to change without prior notice. Please check www.barco.com for the latest specifications.