


Evo20

High-resolution business presentation projector



The evo20 has been designed for business users and corporations. With SXGA+ resolution DLP® technology and unmatched compatibility, it works with virtually anything you connect it to. No more nervous presenters or support calls when you can't get an image projected. With almost double the workspace of regular XGA, SXGA+ provides very wide compatibility, from high resolution notebook and laptop computers to graphics workstations.

RealColor color management suite

The RealColor color management suite ensures perfect color reproduction and allows the user to define a desired white point, or match the colors from the projector to the picture on the screen or a print for true color imaging. Product presentations and corporate profiles look as good as they do in real life and on printed paper. In the evo20, RealColor makes further use of VIDITM lamp technology to enhance colors, and sustain image quality over time.

Professional quality video

With built-in high performance video processing, the evo20 provides professional quality video in all settings, both with analog and digital sources.

Great image quality

The most important thing about your presentation is how you communicate your message, and how it is perceived by the audience. Thanks to the VIDITM lamp and RealColor color management technologies, the evo20 provides outstanding colors, and picture accuracy.

Low operating noise

In many challenging environments, the noise of a projector can be disturbing but this is not the case with the evo20. It is built entirely from magnesium and exotic materials like ceramics to give low noise. The chassis is used for heat dissipation,

In many challenging environments, the noise of a projector can be disturbing but this is not the case with the evo20. It is built entirely from magnesium and exotic materials like ceramics to give low noise. The chassis is used for heat dissipation, and all moving parts are decoupled from the chassis in order to make the least noise.

Simple and secure asset management

Built-in networking allows remote asset management through a simple web interface, or through our dedicated ProNet.Manager asset management software. It also allows easy integration into IP and RS232C based control systems. Familiar, 4-digit pin code password protection prevents unauthorised use.

High performance optics

The precision ground zoom lens features lens shift for distortion free imaging, excellent sharpness and focus from one of the world's leading lens makers. Front access lamp replacement reduces maintenance needs and operating costs in any installation.

Perfectly fit for a wide range of applications

Not only is the evo20 perfectly fit for business presentations, it is also perfect for detailed presentations, such as financial models, product visualisation, database management, engineering and R&D, as well as any graphically demanding work.