

CNWU-61B

6,000 ANSI lumens, WUXGA, single-chip DLP projector



6K
LUMENS

1
CHIP
DLP

Whether your organization is a business, educational or governmental institution, investing in equipment that improves decision-making processes without compromising on ergonomics is important. The CNWU-61B provides razor-sharp, stable and high contrast images that don't tire your eyes and thanks to its low noise levels, working in an environment with front projection has never been more comfortable and productive. And as it comes in a compact and stylish design, it will perfectly match the interior of your meeting room.

Premium image quality

As the CNWU-61B displays crisp images with a high contrast -thanks to its high-quality lenses and optical design -it will turn your meeting room into a professional environment. Thanks to its standard WUXGA resolution, the projector supports any computer graphics or video centric content and will display a crystal clear image.

Zero worries

The CNWU-61B has a filter-free design, an energy-efficient and flexible dual lamp system and uses the acknowledged DLP® technology for unmatched accuracy. Operating the projector in single lamp mode provides you with 5,000 worry-free hours of operation without component replacements. These factors allow you to reduce your installation and maintenance cost significantly.

Product specificaties

CNWU-61B

General specifications	
Type projector	WUXGA single-chip DLP projector
Technologie	LVDC DMD™ with DarkChip3™
Resolutie	1,920 x 1,200 (WUXGA)
Helderheid	6,000 ANSI lumens
Contrastverhouding	6,500:1
Helderheidsuniformiteit	>90%
Beeldverhouding	16:10
Type lens	All pure glass lenses
Lenzen	0.79:1 EN12 ultra wide; 0.8-1.21:1 EN46 ultra wide zoom lens; 1.24-1.6:1 EN13 wide angle zoom lens; 1.6-2.32:1 EN11 standard zoom lens
Optische lensverschuiving	Vertical: -134% to +134%; Horizontal: -68% to +68% (on zoom lenses)
Kleurcorrectie	RealColor™
Lampen	2 x 300W UHP Vidi
Levensduur lamp	Up to 2,000 hours (full power) / Up to 2,500 hours (eco mode)
Lampgarantie (vervanging op locatie/in de fabriek)	500 hours or 90 days
Verzegelde DLP™-kern	Yes
Oriëntatie	table -ceiling
Geïntegreerde webserver	Yes
3D	Passive polarized and Infitec (2 projectors)
Ingangen	1 x DVI-D; 1 x HDMI 1.3a; 1 x VGA; 1 x 5-BNC; 1 x HMDI 1.3a; 1x YPbPr; 1 x S-video; 1 x composite
Invoerresoluties	1,920 x 1,200 -640 x 480 pixel resolution; RGBHV, RGBS, RGsB; custom formats available; HDTV (1080p, 1080i, 720p); NTSC, PAL, SECAM
Max. pixelklok	165 MHz
Softwaretools	Projector Toolset, ProNet
Controle	Minijack + IR, RS232, Network, 12v trigger
Netwerkverbinding	10/100 base-T, RJ-45 connection
Voedingsvereisten	100-240V / 50-60Hz
Max. energieverbruik	850W
Geluidsniveau (standaard bij 25°C/77°F)	41.9dB (ISO 9296)
Operationele omgevingstemperatuur	10-40°C / 50°-104°F
Operationele vochtigheid	20-80% RH
Dissipatie BTU	max 2,900 BTU/h
Afmetingen (B x L x H)	510 x 233 x 376 mm / 20.08 x 9.17 x 14.80 inches
Gewicht	12.6 kg (27.8 lbs)
Verzendingsafmetingen (L x B x H)	520 x 370 x 780 mm / 20.47 x 14.57 x 30.71 inches
Verzendgewicht af fabriek	20 kg (44 lbs)
Standaardaccessoires	Power cord, wireless remote control
Certificeringen	Compliant with FCC, part 15 Class A and CCC, cCSAus, cUL, UL and CE
Garantie	Limited 3 years parts and labor.

Laatst bijgewerkt: 09 Jul 2024

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer www.barco.com voor de nieuwste specificaties.

