

# SP4K-12C

12,000 lumens smart cinema projector



12K  
LUMENS

4K  
4096X2160



- Brilliant image
- Ready for tomorrow, today
- Barco EcoPure™
- Fit and forget

SP4K-12C is part of the Series 4 portfolio, designed in close collaboration with industry partners. Market trends in content creation, exhibition and technology were taken into account. The result? A 4K RGB projector family, designed for cinema.

#### Brilliant image

The Series 4 brings native 4K resolution, higher contrast and enhanced uniformity into the movie theater. The Barco Active Image Management™ and its patented precision brightness technology guarantees flawless images with automatic white balances.

#### Ready for tomorrow, today

The Barco Colorgenic™ technology opens up the full P3 color space and more than 98.5% of Rec. 2020. SP4K-12C is fully enabled for future innovations like 4K 120fps and HDR images. Deliver stunning results not only on day 1, but consistently throughout the lifetime of the product.

#### Barco EcoPure™

This silent running projector (50dB(A)) is fully ready for boothless operation. In addition, the SP4K-12C smartly manages its power consumption of only 8 lm/W. In eco-mode it consumes even less than 3 Watt. What's more, remote wake up on LAN is possible for scheduled maintenance or ingest.

#### Fit and forget

The modular design of the Series 4 projectors allows for cost-effective maintenance. There are only six Barco laser plate™ spare parts to service all light source configurations. Anyone can replace the filters thanks to the toolless cover and filter handling. The SP4K-12C seamlessly integrates into your current setup.

#### Freedom of choice

The SP4K models come in many different configurations offering you the freedom of choice. A range of lumens, compatibility with both Barco lenses and selected 3rd party lenses, and optional touch displays. Play with the available options to match your specific needs.

**Product specificaties****SP4K-12C****General specifications**

|                                       |   |
|---------------------------------------|---|
| Native helderheid                     | 12,000 lumens (typical)   |
| Native contrastverhouding             | 2300:1 (typical)<br><br>up to 3000:1 with HC lens   |
| Digital MicroMirror Device™           | 3x 0.98" DC4K   |
| Resolutie                             | native 4K: 4096 x 2160  |
| Kleurenspectrum                       | DCI P3 compliant (98.5% of Rec.2020; when measured in xy-color coordinates)   |
| Lichtbron                             | Laser   |
| Primelenzen                           | With C-lensholder: 0.8 -1.16; 1.09 -1.40; 1.2 -1.8; 1.4 -2.05; 1.6 -2.5 ; 1.95 -3.2; 2.4 -3.9<br>With B-lensholder: 1.01; 1.27; 1.6 - 2.4; 1.9 - 2.6; 2.0 - 2.95; 2.3 - 3.65; 2.8 - 4.7; 3.55 - 6.95<br>High-brightness and High-contrast B-lenses compatible |
| Langdurige stabiliteit van helderheid | 40,000 hrs @ average usage conditions   |
| Behuizing                             | integrated cooling design and patented sealed optical assembly  |
| Afmetingen (B x L x H)                | Projector incl feet: 710 x 1070 x 547 mm/ 27,95 x 42,13 x 21,54 inches<br>(710 x 1132x 547 mm/ 27,95 x 44.55x 21,54 inches with B-lensholder)   |
| Gewicht                               | 90kg / 198.5lbs   |
| Voedingsvereisten                     | single phase or triple phase 200-240V 16A   |
| Warmtebelasting (max. vermogen)       | 4600 BTU/h  |
| Luchtuitstroom                        | 300 CFM   |
| Omgevingstemperatuur                  | 40°C/104F Max.  |
| Omgevingsvochtigheid                  | 85% RH max  |
| Mediaserver                           | Barco Alchemy ICP-X and other media server brands** supported.  |
| Energieverbruik                       | 1.4kW (3W in Eco mode)  |
| Geluidsniveau                         | 50dB(A) @1m and 25°C ambient temperature  |
| 3D-systemen                           | Active glasses systems and polarization systems on silver screens are supported. Color separation systems are not supported.  |
| Veiligheidsvereisten                  | Class 1 risk group 3  |
| Gebruikersinterface                   | Touch Display and / or web-based  |
| Laterale lenskleur op beeldrand       | With 2K lens: 2 pixels average*<br>With 4K lens: 1.5 pixels average*<br>(* depends on lens, zoom, ...)  |
| Opmerkingen                           | **projector configuration with ICP-D; contact Barco service for the list of supported brands  |

**Laatst bijgewerkt: 05 Jul 2024**

© 2024 Barco nv. Alle rechten voorbehouden. Gehele of gedeeltelijke reproductie zonder schriftelijke toestemming is verboden. Alle merknamen en productnamen zijn handelsmerken, geregistreerde handelsmerken of handelsnamen van hun respectieve houders. Als gevolg van voortdurende innovatie kunnen informatie en technische specificaties zonder voorafgaande kennisgeving worden gewijzigd. Controleer [www.barco.com](http://www.barco.com) voor de nieuwste specificaties.